

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0395345710

Status:

Active

Overview:

Eurostyle Terminal Blocks

Description:

5.08mm Pitch Eurostyle Horizontal Plug, with Retention Screws and Reverse Imprinting, Green Housing, Gold (Au) Plated, 10 Circuits

Documents:

3D Model

3D Model (PDF)

Drawing (PDF)

Product Specification PS-39500-001-001 (PDF)

RoHS Certificate of Compliance (PDF)

Agency Certification

UL

E48521

General

Product Family

Series

Application

Comments

Component Type

Overview

Product Name

Type

UPC

Terminal Blocks

39534

N/A

with Reverse Imprinting

Plug

Eurostyle Terminal Blocks

ESE, Eurostyle Pluggable

Euro Block

822350486576

Physical

Circuits (Loaded)

Entry Angle

Lock to Mating Part

Number of Rows

Orientation

Panel Mount

Pitch - Mating Interface

Pitch - Termination Interface

Polarized to Mating Part

Stackable

Temperature Range - Operating

Wire Size AWG

Wire Size mm²

10

Vertical

Yes

1

Horizontal

No

5.08mm

5.08mm

Yes

No

-40° to +105°C

12, 14, 16, 18, 20, 22, 24, 26

0.13-3.31

Electrical

Current - Maximum per Contact

Voltage - Maximum

18.0A

300V

Solder Process Data

Lead-freeProcess Capability

N/A

Material Info


Reference - Drawing Numbers

Product Specification

Sales Drawing

PS-39500-001-001

SD-39534-001



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

Not Reviewed

Not Relevant

Not Reviewed

Search Parts in this Series

39534 Series

Mates With

Most 5.08mm Pitch Industry Standard PCB Headers, [39535](#) Vertical PCB Header with Threaded Retention Inserts, [39536](#) Horizontal PCB Header with Threaded Retention Inserts

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[39534-5710](#)