

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0395945015

Status:

Active

Overview:

Description:

5.08mm Pitch Eurostyle Vertical Fixed Mount PCB Terminal Block, with Standard Imprinting, Green Housing, 15 Circuits

EU ELV

Not Relevant

EU RoHS

China RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China ROHS

Not Reviewed

ELV

Not Relevant

RoHS Phthalates

Not Reviewed

Search Parts in this Series

39594 Series

Agency Certification	
UL	E48521
General	
Product Family	Terminal Blocks
Series	39594
Application	N/A
Comments	with Standard Imprinting
Component Type	One Piece
Overview	eurostyle_terminal_blocks
Product Name	ESE, Eurostyle Fixed Mount
Type	Euro Block
UPC	822350503846
Physical	
Circuits (Loaded)	15
Entry Angle	Horizontal
Lock to Mating Part	None
Number of Rows	1
Orientation	Vertical
PC Tail Length	3.00mm
PCB Thickness - Recommended	2.00mm
Panel Mount	No
Pitch - Mating Interface	5.08mm
Pitch - Termination Interface	5.08mm
Polarized to Mating Part	N/A
Stackable	No
Temperature Range - Operating	-40° to +105°C
Wire Size AWG	12, 14, 16, 18, 20, 22
Wire Size mm²	0.33-3.31
Electrical	
Current - Maximum per Contact	15.0A
Voltage - Maximum	300V
Solder Process Data	
Duration at Max. Process Temperature (seconds)	005
Lead-freeProcess Capability	REFLOW
Max. Cycles at Max. Process Temperature	135
Process Temperature max. C	260
Material Info	
Reference - Drawing Numbers	
Sales Drawing	SD-39544-001-001

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

39594-5015