

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0399400308

Status:

Active

Overview:

Eurostyle Terminal Blocks

Description:

5.08mm Pitch Beau EuroMate Pluggable PCB Terminal Block, Dual Level, 270° Wire Entry, 8 Circuits

Documents:

3D Model

3D Model (PDF)

Drawing (PDF)

Product Specification PS-39940-001-001 (PDF)

RoHS Certificate of Compliance (PDF)

Agency Certification

UL

E48521

General

Product Family

Series

Application

Comments

Component Type

Overview

Product Name

Type

UPC

Terminal Blocks

39940

N/A

Gold plating available

Plug

Eurostyle Terminal Blocks

EuroMate Pluggable

Euro Block

800756372426

Physical

Circuits (Loaded)

Color - Resin

Entry Angle

Flammability

Lock to Mating Part

Material - Resin

Number of Rows

Orientation

Panel Mount

Pitch - Mating Interface

Pitch - Termination Interface

Polarized to Mating Part

Stackable

Temperature Range - Operating

Termination Interface: Style

Wire Size AWG

Wire Size mm²

8

Black

Horizontal

94V-0

None

Nylon

2

Vertical

No

5.08mm

5.08mm

Yes

No

130°C

Screw or Lug

12, 14, 16, 18, 20, 22

0.50-2.50

Electrical

Current - Maximum per Contact

Voltage - Maximum

15.0A

300V

Material Info

Engineering Number

940908


Reference - Drawing Numbers

Product Specification

Sales Drawing

PS-39940-001-001

SD-39940-005



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Not Reviewed

REACH SVHC

Not Contained Per -ED/88/2018 (15 January 2019)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China RoHS

Green Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

39940 Series

Mates With

395310008 , 395311008 , 395320008 , 395321008

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

39940-0308