

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: **0430300004**
Status: **Active**
Overview: Micro-Fit Connector System
Description: Micro-Fit 3.0 Crimp Terminal, Female, with Tin (Sn) Plated Phosphor Bronze Contact, 26-30 AWG, Reel

Documents:

Drawing (PDF)	Test Summary 430450005-TS-000 (PDF)
Product Specification 430450001-PS-KO-000 (PDF)	Test Summary TS-43045-001-001 (PDF)
Product Specification 430450001-PS-SP-000 (PDF)	Datasheet (PDF)
Product Specification PS-43045-001 (PDF)	RoHS Certificate of Compliance (PDF)
Packaging Specification PK-43030-001-001 (PDF)	

General

Product Family	Crimp Terminals
Series	43030
Application	Power, Wire-to-Board, Wire-to-Wire
Crimp Quality Equipment	Yes
Overview	<u>Micro-Fit Connector System</u>
Packaging Alternative	430300010 (Loose)
Product Name	Micro-Fit 3.0
UPC	800754320092

Physical

Gender	Female
Material - Metal	Phosphor Bronze
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	0.061/g
Packaging Type	Reel
Plating min - Mating	1.016µm
Plating min - Termination	1.016µm
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	1.27mm max.
Wire Size AWG	26, 28, 30
Wire Size mm ²	N/A

Electrical

Current - Maximum per Contact	8.5A
-------------------------------	------

Solder Process Data

Lead-freeProcess Capability	N/A
-----------------------------	-----

Material Info

Reference - Drawing Numbers

Packaging Specification	PK-43030-001-001
Product Specification	430450001-PS-KO-000, 430450001-PS-SP-000, PS-43045-001
Sales Drawing	SD-43030-XXXX-001
Test Summary	430450005-TS-000, TS-43045-001-001



Series image - Reference only

EU ELV

Compliant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
D(2021)4569-DC (8
July 2021)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Compliant

Not Contained

Search Parts in this Series

43030 Series

Use With

Micro-Fit 3.0 Receptacle Housings [43025](#)
, [43645](#)
Micro-Fit BMI Panel Mount
Receptacle Housings [44133](#) , [46623](#)

Micro-Fit TPA Receptacle Housing
[171850](#) , [172952](#)

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description

Product #

Extraction Tool for Micro-Fit Terminals	11030043
Insertion Tool for Micro-Fit 3.0 and CRC Male and Female Crimp	638120800

Terminals, 20-30
 AWG
 PremiumGrade Hand638190000
 Crimp Tool for Micro-
 Fit 3.0 Terminals,
 20-30 AWG
 FineAdjust Applicator639004400
 for Insulation OD
 1.12-1.27mm, 26-30
 AWG Wire
 FineAdjust Applicator639046600
 for Micro-Fit 3.0
 Crimp Terminals,
 Insulation OD
 0.63-1.10mm 26-30
 AWG
 T2 Terminator 639104400
 for Insulation OD
 1.12-1.27mm, 26-30
 AWG

Japan

Description	Product #
Applicator for M21 1A Bench Press, 20-30	<u>572983000</u>
AWG Wire S-1 Applicator for	<u>572983710</u>
Micro-Fit 3.0 Plug and Receptacle Crimp Terminals, 26-30 AWG	

This document was generated on 09/14/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[43030-0004](#)