

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0430310005](#)
Status: **Active**
Overview: [Micro-Fit Connector System](#)
Description: Micro-Fit 3.0 Crimp Terminal, Male, with 0.38µm Select Gold (Au) Plated Phosphor Bronze Contact, 26-30 AWG, Reel

Documents:

Drawing (PDF)	Test Summary 430450006-TS-000 (PDF)
Product Specification 430450001-PS-KO-000 (PDF)	Test Summary TS-43045-001-001 (PDF)
Product Specification 430450001-PS-SP-000 (PDF)	Test Summary TS-43045-002-001 (PDF)
Product Specification PS-43045-001 (PDF)	Test Summary TS-46235-001-001 (PDF)
Packaging Specification PK-43031-001-001 (PDF)	Datasheet (PDF)
Test Summary 430450005-TS-000 (PDF)	RoHS Certificate of Compliance (PDF)

General

Product Family	Crimp Terminals
Series	43031
Application	Power, Wire-to-Wire
Crimp Quality Equipment	Yes
Overview	Micro-Fit Connector System
Packaging Alternative	430310011 (Loose)
Product Name	Micro-Fit 3.0
UPC	800754369497

Physical

Gender	Male
Material - Metal	Phosphor Bronze
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Net Weight	0.048/g
Packaging Type	Reel
Plating min - Mating	0.381µm
Plating min - Termination	2.540µm
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	1.27mm max.
Wire Size AWG	26, 28, 30
Wire Size mm²	N/A

Electrical

Current - Maximum per Contact	8.5A
-------------------------------	------

Material Info

Reference - Drawing Numbers

Packaging Specification	PK-43031-001-001
Product Specification	430450001-PS-KO-000, 430450001-PS-SP-000, PS-43045-001
Sales Drawing	SD-43031-XXXX-001
Test Summary	430450005-TS-000, 430450006-TS-000, TS-43045-001-001, TS-43045-002-001, TS-46235-001-001



Series image - Reference only

EU ELV

Compliant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
D(2021)4569-DC (8
July 2021)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Compliant

Not Contained

Search Parts in this Series

[43031](#) Series

Use With

Micro-Fit 3.0 Plug Housings [43020](#) , [43640](#)

Micro-Fit BMI Plug Housings [44300](#) ,
[46625](#)

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description

Product #

Extraction Tool for
Micro-Fit Terminals

[11030043](#)

Insertion Tool for
Micro-Fit 3.0 and
CRC Male and
Female Crimp
Terminals, 20-30
AWG

[638120800](#)

PremiumGrade Hand	<u>638190000</u>
Crimp Tool for Micro-Fit 3.0 Terminals, 20-30 AWG	
FineAdjust Applicator	<u>639004400</u>
for Insulation OD 1.12-1.27mm, 26-30 AWG Wire	
FineAdjust Applicator	<u>639046600</u>
for Micro-Fit 3.0 Crimp Terminals, Insulation OD 0.63-1.10mm 26-30 AWG	
T2 Terminator	<u>639104400</u>
for Insulation OD 1.12-1.27mm, 26-30 AWG	
Japan	
Description	Product #
S-1 Applicator for Micro-Fit 3.0 Plug and Receptacle Crimp Terminals, 26-30 AWG	<u>572983710</u>

This document was generated on 11/11/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

[43031-0005 \(Cut Strip\)](#) [43031-0005 \(Mouser Reel\)](#)