

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [0436400201](#)  
**Status:** **Active**  
**Overview:**  
**Description:** Micro-Fit 3.0 Plug Housing, Single Row, 2 Circuits, UL 94V-0, Low-Halogen, Black

**Agency Certification**

CSA	LR19980
UL	E29179

**General**

Product Family	Crimp Housings
Series	<a href="#">43640</a>
Application	Power, Wire-to-Wire
Overview	microfit_30
Product Name	Micro-Fit 3.0
UPC	800754366120

**Physical**

Circuits (maximum)	2
Color - Resin	Black
Flammability	94V-0
Gender	Plug
Glow-Wire Capable	No
Keying to Mating Part	None
Lock to Mating Part	Yes
Material - Resin	Nylon
Net Weight	0.333/g
Number of Rows	1
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	3.00mm
Polarized to Mating Part	Yes
Stackable	No
Temperature Range - Operating	-40° to +105°C

**Solder Process Data**

Lead-freeProcess Capability	N/A
-----------------------------	-----

**Material Info**

**Reference - Drawing Numbers**

Packaging Specification	PK-43640-003-001
Product Specification	PS-43650-001
Sales Drawing	SD-43640-XXXX
Test Summary	430450005-TS-000, TS-43045-001-001, TS-43045-002-001, TS-43045-003-001, TS-46235-001-001

**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Not Contained Per -  
D(2020)4578-DC (25  
June 2020)

**Halogen-Free**

**Status**

**Low-Halogen**

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

**China RoHS**

Green Image

Not Relevant

Not Contained

**Search Parts in this Series**

[43640](#) Series

**Mates With**

Micro-Fit 3.0 Receptacle Housing [43645](#)  
 <br>Micro-Fit TPA Cable Assembly [145132](#)  
 <br>Micro-Fit 3.0 Cable Assembly [214750](#) ,  
[214751](#)

**Use With**

Micro-Fit 3.0 Crimp Terminals [43031](#) <br>  
 Micro-Fit 3.0 Pre-Crimped Lead [214762](#) ,  
[214763](#)

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[43640-0201](#)