

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0438796039

Status:

Active

Overview:

Mini-Fit Family Power Connectors

Description:

Mini-Fit BMI Header Compliant Pin Interface, Dual Row, Vertical, 10 Circuits, Make First/Break Last, Tin (Sn) over Nickel Plating, Press Fit Tail

Documents:

3D Model

Drawing (PDF)

3D Model (PDF)

Product Specification PS-43879-001-001 (PDF)

Packaging Specification PK-43879-001-000 (PDF)

Test Summary TS-43879-001-001 (PDF)

RoHS Certificate of Compliance (PDF)

Agency Certification	
CSA	LR19980
UL	E29179
General	
Product Family	PCB Headers
Series	43879
Application	Board-to-Board, Power, Wire-to-Board
Comments	Square Pin Compliant Pin
Overview	Mini-Fit Family Power Connectors
Product Name	Mini-Fit BMI
UPC	884982710078

Physical	
Breakaway	No
Circuits (Loaded)	10
Circuits (maximum)	10
Color - Resin	Black
Durability (mating cycles max)	30
First Mate / Last Break	Yes
Flammability	94V-0
Glow-Wire Capable	No
Guide to Mating Part	No
Keying to Mating Part	None
Lock to Mating Part	Yes
Material - Metal	Brass, Phosphor Bronze
Material - Plating Mating	Tin
Material - Plating Termination	Nickel
Material - Resin	High Temperature Thermoplastic
Net Weight	5.439/g
Number of Rows	2
Orientation	Vertical
PC Tail Length	6.25mm
PCB Locator	No
PCB Retention	Yes
Packaging Type	Tray
Pitch - Mating Interface	4.20mm
Pitch - Termination Interface	4.20mm
Polarized to Mating Part	Yes
Polarized to PCB	No
Shrouded	Fully
Stackable	No
Surface Mount Compatible (SMC)	No
Temperature Range - Operating	-40° to +105°C
Termination Interface: Style	Through Hole - Compliant Pin



Series image - Reference only

EU ELV	
Not Relevant	
EU RoHS	
Compliant	
China RoHS	
REACH SVHC	
Not Contained Per - D(2021)4569-DC (8 July 2021)	
Halogen-Free Status	
Not Low-Halogen	
For more information, please visit Contact US	
China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

43879 Series

Mates With

5557 Mini-Fit Jr. Receptacle Housing, 42385 Mini-Fit BMI Receptacle Header, Mini-Fit BMI Receptacle Housing 42474 , 44516

Electrical

Current - Maximum per Contact	8.0A
Voltage - Maximum	600V AC (RMS)/DC

Solder Process Data

Lead-freeProcess Capability	N/A
-----------------------------	-----

Material Info

Reference - Drawing Numbers

Packaging Specification	PK-43879-001-000
Product Specification	PS-43879-001-001
Sales Drawing	SD-43879-061-000
Test Summary	TS-43879-001-001

This document was generated on 01/03/2022

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

43879-6039