

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0455703002

Status:


Active

Overview:

KK Interconnect Solutions

Description:

3.96mm (.156”) Pitch MarKK Crimp Terminal, 18 to 20 AWG, Tin (Sn) over Nickel (Ni) Plating, Reel



Documents:

Drawing (PDF)

Product Specification PS-45570-001-001 (PDF)

Packaging Specification PK-2759-002-001 (PDF)

Test Summary TS-45570-001-001 (PDF)

RoHS Certificate of Compliance (PDF)

General	
Product Family	Crimp Terminals
Series	45570
Application	Power, Wire-to-Board
Crimp Quality Equipment	Yes
Overview	KK Interconnect Solutions
Packaging Alternative	455703052 (Bag)
Product Name	KK 396, L1NK 396, MarKK
UPC	756054932018
Physical	
Durability (mating cycles max)	25
Gender	Female
Material - Metal	Copper Alloy
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	0.242/g
Packaging Type	Reel
Plating min - Mating	5.080µm
Plating min - Termination	5.080µm
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	3.12mm
Wire Size AWG	18, 20
Wire Size mm²	1.14
Electrical	
Current - Maximum per Contact	13.0A
Voltage - Maximum	600V DC
Material Info	
Reference - Drawing Numbers	
Packaging Specification	PK-2759-002-001
Product Specification	PS-45570-001-001
Sales Drawing	SD-45570-001-001
Test Summary	TS-45570-001-001

EU ELV	
Not Relevant	
EU RoHS	China RoHS
Compliant	
REACH SVHC	
Not Contained Per - D(2021)4569-DC (8 July 2021)	
Halogen-Free	
Status	
Low-Halogen	
For more information, please visit Contact US	
China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

45570 Series

Use With

KK Crimp Terminal Housings [41695](#) , [6442](#) . L1NK 396 Housings [207458](#)

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description	Product #
Extraction Tool for Flat Blade, 3.96mm KK, 2.00mm, 3.96mm EdgeMate, and Ultra-Fit Terminals	11030016
Hand Tool for 3.96mm Crimp Terminals, 18-20 AWG Wire	638193600

FineAdjust Applicator639025700
for 3.96mm (.156")
Pitch MarKK Crimp
Terminal.
FineAdjust Applicator639047900
for 3.96mm (.156")
Pitch MarKK Crimp
Terminal, 18-20
AWG
T2 Terminator for 639125700
Right-Angle, 2.00mm
(.079") Board-in
Terminals

This document was generated on 09/13/2021
PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[45570-3002](#)