

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0459844142

Status:

Active

Overview:

EXTreme LPHPower Connectors

Description:

1.27mm, 12.00mm Pitch, EXTreme LPHPower Receptacle Header, Right-Angle, 4 Power Contacts, 24 Signal Contacts, Select Gold (Au) Plating, for 2.36mm Thick PC Board

Documents:

3D Model

Packaging Specification PK-45984-001-001 (PDF)

Drawing (PDF)

Symbol Footprint Data SYM-45984-4141-001 (PDF)

3D Model (PDF)

RoHS Certificate of Compliance (PDF)

Product Specification PS-45984-001-001 (PDF)

|                                |                                |
|--------------------------------|--------------------------------|
| Agency Certification           |                                |
| CSA                            | LR19980                        |
| UL                             | E29179                         |
| General                        |                                |
| Product Family                 | PCB Receptacles                |
| Series                         | 45984                          |
| Application                    | Board-to-Board, Power          |
| Overview                       | EXTreme LPHPower Connectors    |
| Product Name                   | EXTreme LPHPower               |
| UPC                            | 822350773324                   |
| Physical                       |                                |
| (p)ower-(s)ignal Configuration | 4p - 24s                       |
| Circuits (Loaded)              | 28                             |
| Circuits (maximum)             | 28                             |
| Color - Resin                  | Black                          |
| Durability (mating cycles max) | 250                            |
| Flammability                   | 94V-0                          |
| Glow-Wire Capable              | No                             |
| Guide to Mating Part           | No                             |
| Keying to Mating Part          | Yes                            |
| Lock to Mating Part            | No                             |
| Material - Metal               | High Performance Alloy (HPA)   |
| Material - Plating Mating      | Gold                           |
| Material - Plating Termination | Tin                            |
| Material - Resin               | High Temperature Thermoplastic |
| Net Weight                     | 6.960/g                        |
| Number of Rows                 | 2                              |
| Orientation                    | Right Angle                    |
| PC Tail Length                 | 3.60mm                         |
| PCB Locator                    | No                             |
| PCB Retention                  | None                           |
| PCB Thickness - Recommended    | 2.36mm                         |
| Packaging Type                 | Tray                           |
| Pitch - Mating Interface       | 1.27mm, 12.00mm                |
| Plating min - Mating           | 0.762µm                        |
| Plating min - Termination      | 3.810µm                        |
| Polarized to Mating Part       | Yes                            |
| Polarized to PCB               | Yes                            |
| Stackable                      | No                             |
| Surface Mount Compatible (SMC) | Yes                            |
| Temperature Range - Operating  | -40° to +105°C                 |
| Termination Interface: Style   | Through Hole                   |



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

China RoHS

Compliant

REACH SVHC

Not Contained Per - D(2021)4569-DC (8 July 2021)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

Green Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

45984 Series

Mates With

45985 EXTreme LPHPower Headers, 1.57mm Card Edge

**Electrical**

|                               |         |
|-------------------------------|---------|
| Current - Maximum per Contact | 30.0A   |
| Grounding to PCB              | No      |
| Voltage - Maximum             | 250V AC |

**Solder Process Data**

|                                                |      |
|------------------------------------------------|------|
| Duration at Max. Process Temperature (seconds) | 020  |
| Lead-freeProcess Capability                    | WAVE |
| Max. Cycles at Max. Process Temperature        | 003  |
| Process Temperature max. C                     | 260  |

**Material Info**

**Reference - Drawing Numbers**

|                         |                    |
|-------------------------|--------------------|
| Packaging Specification | PK-45984-001-001   |
| Product Specification   | PS-45984-001-001   |
| Sales Drawing           | SD-45984-400-001   |
| Symbol/Footprint Data   | SYM-45984-4141-001 |

This document was generated on 01/11/2022

**PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION**

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

45984-4142