

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0460121141

Status:

Active

Overview:

Mini-Fit Family Power Connectors

Description:

Mini-Fit Plus Crimp Terminal, 18-20 AWG, Reel, Tin (Sn) Plating

Documents:

Drawing (PDF)

Product Specification PS-45750-001-001 (PDF)

Packaging Specification PK-46012-001-001 (PDF)

RoHS Certificate of Compliance (PDF)

General	
Product Family	Crimp Terminals
Series	46012
Application	Power, Wire-to-Wire
Comments	Current = 13A max. per circuit when header is mated to a receptacle loaded with 45750 series terminals crimped to 16 AWG wire. . See Molex product specification PS-45750-001 for additional current de-rating information.
Crimp Quality Equipment	Yes
Overview	Mini-Fit Family Power Connectors
Packaging Alternative	460121142 (Bag)
Product Name	Mini-Fit Plus
UPC	822350570435
Physical	
Durability (mating cycles max)	100
Gender	Male
Material - Metal	Copper Alloy
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	0.145/g
Packaging Type	Reel
Plating min - Mating	2.540µm
Plating min - Termination	2.540µm
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	1.65-2.95mm
Wire Size AWG	18, 20
Wire Size mm²	N/A
Electrical	
Current - Maximum per Contact	13.0A
Voltage - Maximum	600V
Solder Process Data	
Lead-freeProcess Capability	N/A
Material Info	
Reference - Drawing Numbers	
Packaging Specification	PK-46012-001-001
Product Specification	PS-45750-001-001
Sales Drawing	SD-46012-001-001



Series image - Reference only

EU ELV

Compliant

EU RoHS

Compliant

REACH SVHC

Not Contained Per - D(2021)4569-DC (8 July 2021)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China RoHS

Green Image

ELV

Compliant

RoHS Phthalates

Not Contained

Search Parts in this Series

46012 Series

Use With

Mini-Fit Jr. Plugs 5559
 Mini-Fit MBI Panel Mount Plugs 42475
 Mini-Fit TPA Plugs 30068

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description	Product #
Extraction Tool for Mini-Fit Jr. Terminals	11030044
PremiumGrade HandCrimp Tool for Mini-Fit Jr. Male and Female Terminals, 18-24 AWG	638190901
FineAdjust Applicator for 18-20	639015600

AWG and 18-24
AWG Wires with
Insulation Diameter
1.90-2.30mm
FineAdjust Applicator[639023900](#)
for Insulation OD
1.40-1.70mm - 18-24
AWG
FineAdjust Applicator[639024800](#)
for Insulation OD
2.50-2.95mm
Optimized for 18
AWG Only
FineAdjust Applicator[639024900](#)
for Insulation OD
2.30-2.60mm - 18-24
AWG
FineAdjust Applicator[639047800](#)
for Insulation OD
2.50-2.95mm, 18-24
AWG
FineAdjust Applicator[639048000](#)
for Insulation OD
1.65-2.05mm, 18-24
AWG
T2 Terminator [639115600](#)
for insulation OD
1.90-2.30mm - 18-24
AWG
T2 Terminator [639123900](#)
for insulation OD
1.40-1.70mm - 18-24
AWG
T2 Terminator [639124800](#)
for insulation OD
2.50-2.95mm
optimized for 18
AWG only
T2 Terminator [639124900](#)
for insulation OD
2.30-2.60mm - 18-24
AWG
T2 Terminator [639147800](#)
for Mini-Fit Crimp
Terminals, 18-24
AWG with Large
Insulation ODs
T2 Terminator [639148000](#)
for Mini-Fit Crimp
Terminals, 18-24
AWG with Smaller
Insulation ODs

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

[46012-1141 \(Mouser Reel\)](#) [46012-1141 \(Cut Strip\)](#)