

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0460182541](#)
Status: **Active**
Overview: [Mini-Fit Family Power Connectors](#)
Description: Mini-Fit Plus High Mating Cycle Female Crimp Terminal, 22-24 AWG, Reel, Select Gold (Au) Plating with Proprietary Molex Advanced Contact Surface Finish (CSF) in Contact Area

Documents:

Drawing (PDF)	Test Summary TS-46018-001-001 (PDF)
Product Specification PS-46018-004-001 (PDF)	RoHS Certificate of Compliance (PDF)
Packaging Specification PK-46018-001-001 (PDF)	

General

Product Family	Crimp Terminals
Series	46018
Application	Power, Wire-to-Board, Wire-to-Wire
Comments	Current Rating = 5A Max. Using 22 AWG Wire and 4A Max. Using 24 AWG Wire
Crimp Quality Equipment	Yes
Overview	Mini-Fit Family Power Connectors
Packaging Alternative	460182542 (Loose)
Product Name	Mini-Fit Plus
UPC	822350560450

Physical

Gender	Female
Material - Metal	Copper Alloy
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Net Weight	0.150/g
Packaging Type	Reel
Plating min - Mating	0.051µm
Plating min - Termination	2.540µm
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	1.20-1.80mm
Wire Size AWG	22, 24
Wire Size mm²	N/A

Electrical

Current - Maximum per Contact	13.0A
Voltage - Maximum	600V

Solder Process Data

Lead-freeProcess Capability	N/A
-----------------------------	-----

Material Info

Reference - Drawing Numbers

Packaging Specification	PK-46018-001-001
Product Specification	PS-46018-004-001
Sales Drawing	SD-46018-001-001
Test Summary	TS-46018-001-001



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

China RoHS

REACH SVHC

Not Contained Per -
D(2021)4569-DC (8
July 2021)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

Green Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

[46018](#) Series

Mates With

Mini-Fit Plus Crimp Terminal [46012](#)

Mini-Fit Plus Header [46011](#) , [46014](#)
, [46015](#)
Mini-Fit BMI Header [44068](#) ,
[42404](#) , [43810](#)
Mini-Fit Jr. Header [5569](#)

Mini-Fit TPA Header [30070](#)

Use With

Mini-Fit Jr. Receptacles [5557](#)
Mini-Fit TPA Receptacles [30067](#)
Mini-Fit BMI Panel Mount Receptacles [42474](#)
Mini-Fit BMI Panel Mount Slide-N-Lock Receptacles [44516](#)

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description

Product #

Extraction Tool for [11030044](#)
Mini-Fit Jr. Terminals
PremiumGrade Hand[638191000](#)
Crimp Tool for Mini-
Fit Jr. Male and
Female Terminals,
22-28 AWG
FineAdjust Applicator[639002700](#)
for Insulation OD
1.30-1.50mm, 22-28
AWG Wire
FineAdjust Applicator[639020200](#)
for Insulation OD
1.10-1.30mm - 22-28
AWG
FineAdjust Applicator[639023800](#)
for Insulation OD
0.95-1.08mm - 22-28
AWG
T2 Terminator [639102700](#)
for Insulation OD
1.30-1.50mm, 22-28
AWG
T2 Terminator [639120200](#)
for insulation OD
1.10-1.30mm - 22-28
AWG
T2 Terminator [639123800](#)
for insulation OD
0.95-1.08mm - 22-28
AWG

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

[46018-2541 \(Mouser Reel\)](#) [46018-2541 \(Cut Strip\)](#) [46018-2541 \(Loose Piece\)](#)