

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0462350003

Status:

Active

Overview:

Micro-Fit Connector System

Description:

Micro-Fit RMF Reduced Mating Force, Crimp Terminal, Female, with 0.38µm Selective Gold (Au) over Nickel (Ni), 26-30 AWG, without Lubricant

Documents:

- Drawing (PDF)

Product Specification PS-46235-001-001 (PDF)

Packaging Specification PK-46235-001-001 (PDF)

Test Summary 430450006-TS-000 (PDF)
- Test Summary TS-46235-001-001 (PDF)

Datasheet (PDF)

RoHS Certificate of Compliance (PDF)

General

Product Family

Series

Application

Comments

Crimp Quality Equipment

Overview

Product Name

UPC

Crimp Terminals

46235

Power, Wire-to-Board, Wire-to-Wire

Up to 50% reduction in mating force

Yes

Micro-Fit Connector System

Micro-Fit RMF

800756683508

Physical

Durability (mating cycles max)

Gender

Material - Metal

Material - Plating Mating

Material - Plating Termination

Net Weight

Packaging Type

Plating min - Mating

Plating min - Termination

Termination Interface: Style

Wire Insulation Diameter

Wire Size AWG

Wire Size mm²

40

Female

Copper-Zinc-Tin

Gold

Nickel

0.046/g

Reel

0.381µm

1.270µm

Crimp or Compression

1.27mm max.

26, 28, 30

N/A

Electrical

Current - Maximum per Contact

5.0A

Solder Process Data

Lead-freeProcess Capability

N/A

Material Info

Reference - Drawing Numbers

Packaging Specification

Product Specification

Sales Drawing

Test Summary

PK-46235-001-001

PS-46235-001-001

SD-46235-001-001

430450006-TS-000, TS-46235-001-001



Series image - Reference only

EU ELV

Compliant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
D(2021)4569-DC (8
July 2021)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Compliant

Not Contained

Search Parts in this Series

46235 Series

Mates With

Micro-Fit 3.0 Male Crimp Terminals [43031](#)

Use With

Micro-Fit 3.0 Receptacle Housings [43025](#)
, [43645](#) . Micro-Fit BMI Panel Mount
Receptacle Housings [44133](#) . Micro-Fit TPA
Receptacle Housing [172952](#)

Application Tooling | [FAQ](#)

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description

Product #

Extraction Tool for

Micro-Fit Terminals

PremiumGrade Hand

Crimp Tool for Low

Force Micro-Fit 3.0

[11030043](#)

[638192900](#)

Terminals, 20-30
AWG
T2 Terminator 639101300
Tooling Die for Crimp
Terminal, 26-30
AWG Wire

This document was generated on 02/01/2022

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

[46235-0003 \(Mouser Reel\)](#) [46235-0003 \(Cut Strip\)](#) [46235-0003 \(Loose Piece\)](#)