

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0466261305

Status:

Active

Overview:

L1NK Connector System

Description:

L1NK 250 Female Crimp Terminal, 22-24 AWG, Tin (Sn) Plating, Reel

- Documents:
- Drawing (PDF)

Product Specification 2079020001-PS-000 (PDF)

Product Specification 2079020001-PS-CH-000 (PDF)

Product Specification 2079020001-PS-ES-000 (PDF)

Product Specification 2079020001-PS-JP-000 (PDF)

Product Specification 2079020001-PS-SK-000 (PDF)

Application Specification 2079020001-AS-000 (PDF)

Packaging Specification PK-46626-001-001 (PDF)

Test Summary 2079020000-TS-000 (PDF)

Datasheet (PDF)

RoHS Certificate of Compliance (PDF)

General	
Product Family	Crimp Terminals
Series	46626
Application	Power, Wire-to-Board
Crimp Quality Equipment	Yes
Overview	L1NK Connector System
Product Name	L1NK 250
UPC	191130122134
Physical	
Durability (mating cycles max)	25
Gender	Female
Material - Metal	Copper Alloy
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	0.051/g
Packaging Type	Reel
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	1.42mm-1.60mm
Wire Size AWG	22, 24
Wire Size mm²	0.20-0.33

Electrical	
Current - Maximum per Contact	6.5A
Voltage - Maximum	250V AC (RMS)/DC

Material Info

Reference - Drawing Numbers	
Application Specification	2079020001-AS-000
Packaging Specification	PK-46626-001-001
Product Specification	2079020001-PS-000, 2079020001-PS-CH-000, 2079020001-PS-ES-000, 2079020001-PS-JP-000, 2079020001-PS-SK-000
Sales Drawing	466260002-SD-000
Test Summary	2079020000-TS-000



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

China RoHS

REACH SVHC

Not Contained Per -

D(2021)4569-DC (8

July 2021)

Halogen-Free

Status

Low-Halogen

For more information, please visit

Contact US

China ROHS

Green Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

46626 Series

Use With

L1NK 250 Receptacle Housing 207841

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description	Product #
Extraction Tool for L1NK 250 Receptacle Crimp Terminals, 22-28 AWG	2002221000
Hand Crimp Tool for L1NK 250 Female Crimp Terminals, 22-28 AWG, UL1007 Wire	2133090300

FineAdjust Applicator 639047600
for L1NK 250 Female
Crimp Terminal,
22-24 AWG, UL1007
Wire

This document was generated on 09/02/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

46626-1305