

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

47018-2002

Status:

Active

Overview:

Serial ATA Host Receptacles

Description:

1.27mm Pitch Serial ATA Host Receptacle, Mating Height 4.30mm, 0.38µm Gold (Au) Plating, Light Tin Solder Area, Surface Mount, Right Angle, Top Mount Type, 22 Circuits, Lead-Free

Documents:

3D Model

Drawing (PDF)

Product Specification PS-67492-001 (PDF)

RoHS Certificate of Compliance (PDF)




image - Reference only

Series

Agency Certification	
CSA	LR19980
UL	E29179
General	
Product Family	PCB Receptacles
Series	47018
Application	Board-to-Board, Signal
Comments	Top Mount Type
Overview	Serial ATA Host Receptacles
Product Name	Serial ATA
UPC	822350127691

Physical	
Circuits (Loaded)	22
Circuits (maximum)	22
Color - Resin	Black
Durability (mating cycles max)	500
Flammability	94V-0
Glow-Wire Compliant	No
Keying to Mating Part	Yes
Lock to Mating Part	None
Material - Metal	Copper Alloy
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Net Weight	1.907/g
Number of Rows	1
Orientation	Right Angle
PCB Locator	Yes
PCB Retention	Yes
PCB Thickness - Recommended	1.60mm
Packaging Type	Tray
Pitch - Mating Interface	1.27mm
Pitch - Termination Interface	1.27mm
Plating min - Mating	0.381µm
Plating min - Termination	2.032µm
Polarized to Mating Part	Yes
Polarized to PCB	Yes
Surface Mount Compatible (SMC)	N/A
Temperature Range - Operating	-35°C to +85°C
Termination Interface: Style	Surface Mount

Electrical	
Current - Maximum per Contact	1.5A
Voltage - Maximum	15V DC

EU RoHS

ELV and RoHS Compliant

REACH SVHC

Contains SVHC: No

Low-Halogen Status

Not Low-Halogen

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

47018Series

Mates With

87703-0001

Solder Process Data

Lead-free Process Capability	Reflow Capable (SMT only)
Process Temperature max. C	230

Material Info

Reference - Drawing Numbers

Electrical Model Document	EE-47018-003
Product Specification	PS-67492-001
Sales Drawing	SD-47018-001

This document was generated on 11/11/2013

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[47018-2002](#)