

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0483930004](#)
Status: **Active**
Overview: [USB Products and Solutions](#)
Description: Universal Serial Bus (USB 3.0) I/O Receptacle, Right-Angle, Type A, High-Temperature Blue Nylon, Flash Gold (Au) 3µ' Minimum Plating, Contact Height 4.00mm

Documents:
[3D Model](#) [Product Specification TS-48393-001-001 \(PDF\)](#)
[Drawing \(PDF\)](#) [Packaging Specification PK-48393-001 \(PDF\)](#)
[Product Specification PS-48393-001-001 \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

General	
Product Family	I/O Connectors
Series	48393
Application	Wire-to-Board
Component Type	Receptacle
Overview	USB Products and Solutions
Product Name	USB 3.0
Type	A
UPC	887191519203
Physical	
Circuits (Loaded)	9
Color - Resin	Blue
Durability (mating cycles max)	5000
Gender	Female
Keying to Mating Part	Yes
Lock to Mating Part	No
Material - Metal	Copper Alloy
Material - Plating Mating	Nickel, Tin
Material - Plating Termination	Gold
Material - Resin	High Temperature Thermoplastic
Net Weight	3.630/g
Number of Rows	2
Orientation	Right Angle
PC Tail Length	1.10mm
PCB Locator	Yes
PCB Retention	Yes
Packaging Type	Embossed Tape on Reel
Panel Mount	No
Pitch - Mating Interface	2.00mm, 2.50mm
Pitch - Termination Interface	2.00mm, 2.50mm
Polarized to Mating Part	Yes
Polarized to PCB	Yes
Ports	1
Temperature Range - Operating	-20° to +85°C
Termination Interface: Style	Through Hole
Electrical	
Current - Maximum per Contact	1.8A
Grounding to Panel	None
Voltage - Maximum	30V AC/DC

Material Info

Reference - Drawing Numbers
[Packaging Specification](#) PK-48393-001
[Product Specification](#) PS-48393-001-001, TS-48393-001-001



Series image - Reference only

EU ELV Not Relevant	
EU RoHS Compliant REACH SVHC Not Contained Per - ED/71/2019 (16 July 2019) Halogen-Free Status Low-Halogen For more information, please visit Contact US	China RoHS China ROHS ELV RoHS Phthalates
Green Image Not Relevant Not Contained	

Search Parts in this Series
[48393 Series](#)

Mates With
USB 3.0 Type A Plug

This document was generated on 09/18/2019

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[48393-0004](#)