

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0510650700](#)
Status: **Active**
Overview: [Micro-Latch Wire-to-Board Connector System](#)
Description: 2.00mm Pitch, Micro-Latch Receptacle Crimp Housing, Single Row, 7 Circuits, Natural

Documents:	
3D Model (PDF)	Product Specification 510651000-PS-000 (PDF)
3D Model	Product Specification 510651001-PS-000 (PDF)
Drawing (PDF)	Packaging Specification SPK-51065-001-001 (PDF)
Product Specification 510650000-PS-000 (PDF)	RoHS Certificate of Compliance (PDF)
Product Specification 510650001-PS-000 (PDF)	Product Literature (PDF)

Agency Certification	
CSA	LR19980
UL	E29179
General	
Product Family	Crimp Housings
Series	51065
Application	Signal, Wire-to-Board
Overview	Micro-Latch Wire-to-Board Connector System
Product Name	Micro-Latch
UPC	800753574281

Physical	
Circuits (maximum)	7
Color - Resin	Natural
Flammability	94V-0
Gender	Receptacle
Glow-Wire Capable	No
Material - Resin	Polyester
Net Weight	182.600/mg
Number of Rows	1
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	2.00mm
Stackable	No
Temperature Range - Operating	-40° to +105°C

Material Info	
Reference - Drawing Numbers	
Packaging Specification	SPK-51065-001-001
Product Specification	510650000-PS-000, 510650001-PS-000, 510651000-PS-000, 510651001-PS-000
Sales Drawing	510650000-SD-000



Series image - Reference only

EU ELV Not Relevant	
EU RoHS Compliant REACH SVHC Not Contained Per - D(2020)9139-DC (19 Jan 2021) Halogen-Free Status Not Low-Halogen For more information, please visit Contact US	China RoHS China ROHS ELV RoHS Phthalates
Green Image Not Relevant Not Contained	

Search Parts in this Series
[51065](#) Series

Mates With
[53253](#) PCB Header, [53254](#) PCB Header

Use With
[50212](#) Crimp Terminal

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[51065-0700](#)