

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0511140210](#)
Status: **Active**
Overview: [Mighty-SPOX Connector System](#)
Description: Mighty-SPOX Wire-to-Wire Plug Housing, 3.50mm Pitch, Positive Lock, with Optional Panel Mount, 2 Circuits

Documents:
[3D Model](#)
[Drawing \(PDF\)](#)
[3D Model \(PDF\)](#)
[Product Specification PS-51067-008 \(PDF\)](#)
[RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification
CSA LR19980
UL E29179

General
Product Family Crimp Housings
Series [51114](#)
Application Power
Overview [Mighty-SPOX Connector System](#)
Product Name Mighty-SPOX
UPC 800754310031

Physical
Circuits (maximum) 2
Color - Resin Natural
Flammability 94V-0
Gender Plug
Glow-Wire Capable No
Material - Resin Polyester
Net Weight 1059.000/mg
Number of Rows 1
Packaging Type Bag
Panel Mount No
Pitch - Mating Interface 3.50mm
Stackable No
Temperature Range - Operating -40° to +105°C

Material Info
Reference - Drawing Numbers
Product Specification PS-51067-008
Sales Drawing SD-51114-001



Series image - Reference only

EU ELV
Not Relevant

EU RoHS **China RoHS**
Compliant
REACH SVHC
Not Contained Per -
ED/71/2019 (16 July
2019)
Halogen-Free
Status
Not Low-Halogen
For more information, please visit [Contact US](#)

China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series
[51114 Series](#)

Mates With
[51067](#)

Use With
[50419](#)

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[51114-0210](#)