

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0511140910

Status:

Active

Overview:

Mighty-SPOX Connector System

Description:

Mighty-SPOX Wire-to-Wire Plug Housing, 3.50mm Pitch, Positive Lock, with Optional Panel Mount, 9 Circuits



Series image - Reference only

Documents:

3D Model

Drawing (PDF)

3D Model (PDF)

Product Specification PS-51067-008 (PDF)

RoHS Certificate of Compliance (PDF)

Agency Certification		
CSA		LR19980
UL		E29179
General		
Product Family		Crimp Housings
Series		51114
Application		Power
Overview		Mighty-SPOX Connector System
Product Name		Mighty-SPOX
UPC		800754310253
Physical		
Circuits (maximum)		9
Color - Resin		Natural
Flammability		94V-0
Gender		Plug
Glow-Wire Capable		No
Material - Resin		Polyester
Net Weight		3000.000/mg
Number of Rows		1
Packaging Type		Bag
Panel Mount		No
Pitch - Mating Interface		3.50mm
Stackable		No
Temperature Range - Operating		-40° to +105°C
Material Info		
Reference - Drawing Numbers		
Product Specification		PS-51067-008
Sales Drawing		SD-51114-001

EU ELV	
Not Relevant	
EU RoHS	China RoHS
Compliant	
REACH SVHC	
Not Contained Per - ED/71/2019 (16 July 2019)	
Halogen-Free Status	
Not Low-Halogen	
For more information, please visit Contact US	
China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

51114 Series

Mates With

51067

Use With

50419

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

51114-0910