

This document was generated on 12/20/2021

## PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: 0524651271

Status: Active

Overview: SlimStack Board-to-Board/Board-to-FPC Connectors

**Description:** SlimStack Board-to-Board Connector, 0.80mm Pitch, Rigid Type Receptacle, 4.50 to

7.00mm Mated Height, Vertical, 12 Circuits, without Boss

**Documents:** 

3D Model Packaging Specification SPK-52465-002-001 (PDF)

3D Model (PDF)
Drawing (PDF)
Product Guide (PDF)

Product Specification PS-52465-010-001 (PDF)

RoHS Certificate of Compliance (PDF)

Product Specification PS-52465-014-001 (PDF)

Reference Guide (PDF)

Product Specification PS-52465-015-001 (PDF)

General

Product Family PCB Receptacles

Series <u>52465</u>

Application Board-to-Board, Signal

Overview SlimStack Board-to-Board/Board-to-FPC Connectors

Product Name SlimStack
Series Name 0.8 and above
UPC 822348142934

**Physical** 

Circuits (Loaded) 12
Circuits (maximum) 12
Color - Resin Natural
Durability (mating cycles max) 30
Glow-Wire Capable No

Mated Height 4.50mm, 5.65mm, 6.00mm, 7.00mm

Mated Width 4.70mm, 5.10mm Material - Metal Phosphor Bronze

Material - Plating Mating

Tin
Material - Plating Termination

Tin

Material - Resin High Temperature Thermoplastic

Net Weight128.500/mgNumber of Rows2OrientationVerticalPCB LocatorNo

PCB Locator No
PCB Retention None
PCB Thickness - Recommended 1.60mm

Packaging Type Embossed Tape on Reel

Pitch - Mating Interface 0.80mm
Plating min - Mating 1.016µm
Plating min - Termination 1.016µm
Polarized to PCB No
Surface Mount Compatible (SMC) N/A

Temperature Range - Operating -40° to +105°C
Termination Interface: Style Surface Mount


**Electrical** 

Current - Maximum per Contact 0.5A Voltage - Maximum 50V

**Material Info** 

**Reference - Drawing Numbers** 

Packaging Specification SPK-52465-002-001



**EU ELV** 

**Not Relevant** 

EU RoHS China RoHS

Compliant REACH SVHC Not Contained Per -D(2021)4569-DC (8

July 2021) Halogen-Free

**Status** 

**Not Low-Halogen** 

For more information, please visit Contact US

China ROHS Green Image
ELV Not Relevant
ROHS Phthalates Not Contained

Search Parts in this Series

52465 Series

**Mates With** 

53364, 53353, 53307, 53309

This document was generated on 12/20/2021

## PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

## **Mouser Electronics**

**Authorized Distributor** 

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

52465-1271