

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0528072810

Status:


Active

Overview:

Easy-On FFC FPC Connectors

Description:

1.00mm Pitch Easy-On FFC/FPC Connector, Right-Angle, Non-ZIF, Top Contact Style Receptacle, 28 Circuits



|                                |                                                                 |
|--------------------------------|-----------------------------------------------------------------|
| Documents:                     |                                                                 |
| <a href="#">Drawing (PDF)</a>  | <a href="#">Product Specification PS-52807-003-001 (PDF)</a>    |
| <a href="#">3D Model</a>       | <a href="#">Packaging Specification SPK-52807-001-001 (PDF)</a> |
| <a href="#">3D Model (PDF)</a> | <a href="#">RoHS Certificate of Compliance (PDF)</a>            |

|                                |                                |
|--------------------------------|--------------------------------|
| Agency Certification           |                                |
| UL                             | E29179                         |
| General                        |                                |
| Product Family                 | FFC/FPC Connectors             |
| Series                         | 52807                          |
| Overview                       | Easy-On FFC FPC Connectors     |
| Product Name                   | Easy-On                        |
| UPC                            | 800753361188                   |
| Physical                       |                                |
| Actuator Type                  | Non-ZIF                        |
| Circuits (Loaded)              | 28                             |
| Color - Resin                  | Natural                        |
| Contact Position               | Top                            |
| Flammability                   | 94V-0                          |
| Mated Height                   | 3.60mm                         |
| Material - Metal               | Phosphor Bronze                |
| Material - Plating Mating      | Tin                            |
| Material - Plating Termination | Tin                            |
| Material - Resin               | High Temperature Thermoplastic |
| Net Weight                     | 835.801/mg                     |
| Number of Rows                 | 1                              |
| Orientation                    | Right Angle                    |
| PC Tail Length                 | 3.20mm                         |
| PCB Mounting                   | Through Hole - Kinked Pin      |
| PCB Retention                  | None                           |
| Packaging Type                 | Tray                           |
| Pitch - Mating Interface       | 1.00mm                         |
| Pitch - Termination Interface  | 1.00mm                         |
| Plating min - Mating           | 0.914µm                        |
| Plating min - Termination      | 0.914µm                        |
| Polarized to PCB               | Yes                            |
| Stackable                      | No                             |
| Surface Mount Compatible (SMC) | No                             |
| Temperature Range - Operating  | -20° to +80°C                  |
| Wire/Cable Type                | FFC/FPC                        |
| Electrical                     |                                |
| Current - Maximum per Contact  | 0.2A, 0.4A, 0.5A               |
| Voltage - Maximum              | 50V                            |
| Material Info                  |                                |
| Reference - Drawing Numbers    |                                |
| Packaging Specification        | SPK-52807-001-001              |
| Product Specification          | PS-52807-003-001               |

|                                                               |               |
|---------------------------------------------------------------|---------------|
| EU ELV                                                        |               |
| Not Relevant                                                  |               |
| EU RoHS                                                       | China RoHS    |
| Compliant                                                     |               |
| REACH SVHC                                                    |               |
| Not Contained Per - D(2021)4569-DC (8 July 2021)              |               |
| Halogen-Free                                                  |               |
| Status                                                        |               |
| Not Low-Halogen                                               |               |
| For more information, please visit <a href="#">Contact US</a> |               |
| China ROHS                                                    | Green Image   |
| ELV                                                           | Not Relevant  |
| RoHS Phthalates                                               | Not Contained |

Search Parts in this Series

52807 Series

This document was generated on 01/14/2022

**PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION**

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[52807-2810](#)