

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0541324533

Status:

Active

Overview:

Easy-On FFC FPC Connectors

Description:

Easy-On FFC/FPC Connector, 0.50mm Pitch, Slider Series, Right-Angle, Bottom Contact, 2.00mm Height, 45 Circuits, Tin-Silver-Bismuth Plating



- Documents:
- [3D Model \(PDF\)](#)

[Drawing \(PDF\)](#)

[3D Model](#)

[Product Specification PS-54132-062-001 \(PDF\)](#)

[Packaging Specification SPK-54132-001-001 \(PDF\)](#)
- [Datasheet \(PDF\)](#)

[Product Guide \(PDF\)](#)

[RoHS Certificate of Compliance \(PDF\)](#)

[Reference Guide \(PDF\)](#)

Agency Certification	
UL	E29179
General	
Product Family	FFC/FPC Connectors
Series	54132
Overview	Easy-On FFC FPC Connectors
Product Name	Easy-On
Series Name	Slider
UPC	887191270708
Physical	
Actuator Type	Slider
Circuits (Loaded)	45
Color - Resin	Black, Natural
Contact Position	Bottom
Durability (mating cycles max)	20
Flammability	94V-0
Mated Height	2.00mm
Material - Metal	Phosphor Bronze
Material - Plating Mating	Tin-Silver-Bismuth
Material - Plating Termination	Tin-Silver-Bismuth
Material - Resin	Nylon
Net Weight	497.600/mg
Number of Rows	1
Orientation	Right Angle
PC Tail Length	2.00mm
PCB Locator	No
PCB Mounting	Surface Mount
PCB Retention	None
Packaging Type	Embossed Tape on Reel
Pitch - Mating Interface	0.50mm
Pitch - Termination Interface	0.50mm
Polarized to PCB	Yes
Stackable	No
Surface Mount Compatible (SMC)	N/A
Temperature Range - Operating	-40° to +85°C
Wire/Cable Type	FFC/FPC
Electrical	
Current - Maximum per Contact	0.5A
Voltage - Maximum	50V

Material Info

EU ELV	
Not Relevant	
EU RoHS	China RoHS
Compliant	
REACH SVHC	
Not Contained Per - D(2020)9139-DC (19 Jan 2021)	
Halogen-Free	
Status	
Not Low-Halogen	
For more information, please visit Contact US	
China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

54132 Series

Mates With

Premo-Flex FFC Cable [15166](#) , [98266](#) , [15266](#) , [15366](#)

Reference - Drawing Numbers

Packaging Specification	SPK-54132-001-001
Product Specification	PS-54132-062-001
Sales Drawing	541320000-000, 541321000-000

This document was generated on 07/07/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

54132-4533