

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0733660067

Status:

Active

Overview:

MCX RF Connectors

Description:

50 Ohms, MCX Jack Receptacle, Vertical, Straight, 7.10mm Height, 1.57mm Standoff Height, Nickel (Ni) Plated Body, One Piece Per Bag

Documents:

3D Model

3D Model (PDF)

Drawing (PDF)

RoHS Certificate of Compliance (PDF)

General

Product Family

Series

Overview

Product Name

Style

Type

UPC

Wire/Cable Type

RF/Coax Connectors

73366

MCX RF Connectors

MCX

PCB

Microminiature

800756723273

N/A

Physical

Gender

Keying to Mating Part

Net Weight

Orientation

PCB Mounting

PCB Thickness - Recommended

Packaging Type

Panel Mount

Panel Mount Method

Reverse Polar

Jack

None

0.559/g

Straight

Through Hole

1.20mm

Bag

No

N/A

No

Electrical

Frequency

Impedance

Power / Voltage

6 GHz

50Ω

VOLTAGE: 335 Vrms@Sea Level

Material Info

Reference - Drawing Numbers

Sales Drawing

SD-73366-006-001, SD-73366-619-000



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

China RoHS

Compliant with Exemption 6(c)

REACH SVHC

Contained Per - D(2020)9139-DC (19 Jan 2021)

Lead

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

50 Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

73366 Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[73366-0067](#)