

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0587190010

Status:

Active

Overview:

HMC Heavy Duty Rectangular Connectors

Description:

HMC Rectangular Industrial Panel-Mount Bracket, Multi-Module Type, 48-72 Circuits, Type A Polarization

Documents:

3D Model (PDF)

Drawing (PDF)

3D Model

Product Specification PS-58719-006-001 (PDF)

RoHS Certificate of Compliance (PDF)

General

Product Family

Series

Application

Component Type

Overview

Product Name

Type

UPC

I/O Connectors

58719

Panel-Mount

Panel-Mount Bracket

HMC Heavy Duty Rectangular Connectors

HMC

N/A

800753921078

Physical

Boot Color

Circuits (Loaded)

Circuits (maximum)

Durability (mating cycles max)

Gender

Lock to Mating Part

Material - Plating Mating

Net Weight

Number of Rows

Orientation

PCB Locator

Packaging Type

Panel Mount

Pitch - Mating Interface

Polarized to Mating Part

Ports

Surface Mount Compatible (SMC)

Temperature Range - Operating

Termination Interface: Style

Waterproof / Dustproof

Waterproof / Dustproof Type

N/A

N/A

48

50

Receptacle

Yes

N/A

131282.800/mg

2

Vertical

No

Bag

Screws

N/A

Yes

1

N/A

-55° to +125°C

N/A

Yes

IP65

Electrical

Current - Maximum per Contact

Shield Type

Shielded

Voltage - Maximum

20.0A

Full Shield

Yes

300V DC

Material Info

Reference - Drawing Numbers

Product Specification

Sales Drawing

PS-58719-006-001

SD-58719-002-001



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

China RoHS

Compliant with Exemption 6(a)-I,6(b)-II

REACH SVHC

Not Reviewed

Halogen-Free

Status

Low-Halogen

For more information, please visit Contact US

China ROHS

50 Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

58719 Series

Mates With

587210010 Hood Bracket, 58723 Hood

Use With

51202 dust Cover, 51194 Housing, 51195 Housing, 51203 Housing, 51204 Housing

This document was generated on 10/11/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[58719-0010](#)