

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0622018936

Status:

Active

Overview:

Application Tooling

Description:

IMPEL Backplane Press-In Tool


Documents:

RoHS Certificate of Compliance (PDF)

General	
Product Family	Application Tooling
Series	207123
Comments	See Tooling Specification (PDF) Above
Function	Insertion
Geographic Area	Global
Level of Automation	Manual
More Detailed Tech Information	applicationtooling@molex.com
Overview	Application Tooling
Product Name	Impel
Tool Type	Press-Fit Insertion Tool
UPC	887191256474
Warranty Disclaimer	CAUTION: Molex tooling crimp specifications are valid only when used with Molex terminals and tooling manufactured by Molex and sold by Molex or authorized distributors ("Molex Tooling"). When using tooling other than Molex Tooling with Molex specific connector systems listed in our ATS documents, the Molex tooling qualification does not apply and the responsibility for full qualification of the connector system is that of the customer. Molex accepts no liability for connector performance or tooling support where tooling other than Molex Tooling is used or where Molex Tooling is modified.

Material Info

Reference - Drawing Numbers	
Application Tooling Documents	ATS-622018936



Series image - Reference only

EU ELV	
Not Relevant	
EU RoHS	China RoHS
Not Reviewed	
REACH SVHC	
Not Contained Per -ED/01/2018 (15 January 2018)	
Halogen-Free	
Status	
Not Relevant	
For more information, please visit Contact US	
China ROHS	Not Relevant
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

207123 Series

Use With

IMPEL Backplane Assembly, 6-Pair by 12 Column Assemblies, [171495](#)

Application Tooling Description	FAQ Product #
Impel 90 Ohm, 6 Pair Vertical Orthogonal, Backplane Header, 1.85/2.35mm Pitch, Unguided Type B, Dual Endwalls, 12 Columns, 144 Circuits, Pin Length 4.90mm, Plated Through Hole Dimension 0.36mm	1714951227
Impel 90 Ohm, 6 Pair Vertical Orthogonal Backplane Header, 1.85/2.35mm Pitch, Left-Guided Type	1714953207

B, Open Endwalls,
12 Columns, 144
Circuits, Pin Length
4.90mm, Plated
Through Hole
Dimension 0.36mm

This document was generated on 02/27/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[62201-8936](#)