

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0622018952

Status:

Active

Overview:

Application Tooling

Description:

Impel Backplane Module Installation Press-In Tool

Documents:

RoHS Certificate of Compliance (PDF)


General	
Product Family	Application Tooling
Series	207123
Comments	See Tooling Specification (PDF) Above
Function	Insertion
Geographic Area	Global
Level of Automation	Manual, Semi-Automatic
More Detailed Tech Information	applicationtooling@molex.com
Overview	Application Tooling
Product Name	Impel
Tool Type	Press-Fit Insertion Tool
UPC	887191315683
Warranty Disclaimer	CAUTION: Molex tooling crimp specifications are valid only when used with Molex terminals and tooling manufactured by Molex and sold by Molex or authorized distributors ("Molex Tooling"). When using tooling other than Molex Tooling with Molex specific connector systems listed in our ATS documents, the Molex tooling qualification does not apply and the responsibility for full qualification of the connector system is that of the customer. Molex accepts no liability for connector performance or tooling support where tooling other than Molex Tooling is used or where Molex Tooling is modified.

Material Info

Reference - Drawing Numbers

Application Tooling Documents

ATS-622018952



Series image - Reference only

EU ELV	
Not Relevant	
EU RoHS	China RoHS
Not Relevant	
REACH SVHC	
Not Relevant	
Halogen-Free	
Status	
Not Relevant	
For more information, please visit Contact US	
China ROHS	Not Relevant
ELV	Not Relevant
RoHS Phthalates	Not Relevant

Search Parts in this Series

207123 Series

Application Tooling Description	FAQ Product #
Impel 90 Ohm, 4 Pair Vertical Backplane Header, 1.90mm Pitch, Unguided, Open Endwalls, 10 Columns, 80 Circuits, Pin Length 4.90mm, Plated Through Hole Dimension 0.36mm	1713151107
Impel 90 Ohm, 4 Pair Vertical Backplane Header, 1.90mm Pitch, Unguided, Dual Endwalls, 10 Columns, 80 Circuits, Pin Length 5.50mm, Plated Through Hole Dimension 0.36mm	1713151128
Impel 90 Ohm, 4 Pair Vertical Backplane Header, 1.90mm Pitch, Right Guided,	1713155107

10 Columns, 80
Circuits, Pin Length
4.90mm, Plated
Through Hole
Dimension 0.36mm
Impel 90 Ohm, 4 Pair 1713157108
Vertical Backplane
Header, 1.90mm
Pitch, Left Guided,
with Endwall, 10
Columns, 80 Circuits,
Pin Length 5.50mm,
Plated Through Hole
Dimension 0.36mm
Impel 90 Ohm, 4 Pair 1713159108
Vertical Backplane
Header, 1.90mm
Pitch, Right Guided,
with Endwall, 10
Columns, 80 Circuits,
Pin Length 5.50mm,
Plated Through Hole
Dimension 0.36mm

This document was generated on 02/27/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[62201-8952](#)