

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0638017300

Status:

Active

Overview:

Application Tooling

Description:

TM-3000 Universal Crimp Press, 220AC 50/60Hz, Used for product up to 10 AWG

Documents:

RoHS Certificate of Compliance (PDF)

General

Product Family

Series

ApplicationTooling Video

Comments

Function

Geographic Area

Level of Automation

More Detailed Tech Information

Overview

Product Name

Tool Type

UPC

Warranty Disclaimer

Application Tooling

207125

[www.youtube.com/watch?v=1Gj31xD5L\\_c](http://www.youtube.com/watch?v=1Gj31xD5L_c) ,  
[www.youtube.com/watch?v=lj0kZ20\\_wTo](http://www.youtube.com/watch?v=lj0kZ20_wTo) ,  
[www.youtube.com/watch?v=0avd9Rlph58](http://www.youtube.com/watch?v=0avd9Rlph58) ,  
[www.youtube.com/watch?v=LjjqR9hEuNk](http://www.youtube.com/watch?v=LjjqR9hEuNk)

2.0 Ton Press, 30mm press stroke

Crimp

Global

Semi-Automatic

[applicationtooling@molex.com](mailto:applicationtooling@molex.com)

Application Tooling

TM-3000

Electric Press

822350060776

CAUTION: Molex tooling crimp specifications are valid only when used with Molex terminals and tooling manufactured by Molex and sold by Molex or authorized distributors ("Molex Tooling"). When using tooling other than Molex Tooling with Molex specific connector systems listed in our ATS documents, the Molex tooling qualification does not apply and the responsibility for full qualification of the connector system is that of the customer. Molex accepts no liability for connector performance or tooling support where tooling other than Molex Tooling is used or where Molex Tooling is modified.

Physical

Net Weight

114.500/kg

Material Info

Engineering Number

TM3000-220V

Reference - Drawing Numbers

Application Tooling Documents

TM-638000029-001, TM-638000029CN-001,  
TM-638000029DE-001, TM-638000029FR-001,  
TM-638000029IT-001, TM-638000029JP-001,  
TM-638000029KR-001, TM-638000029MY-001,  
TM-638000029PL-001, TM-638000029RU-001,  
TM-638000029SK-001, TM-638000029SP-001,  
TM-638000029TH-001, TM-638000029TW-001,  
TM-638000029VN-001, TM-638017299-001,  
TM-638017299CH-001, TM-638017299DE-001,  
TM-638017299FR-001, TM-638017299IT-001,  
TM-638017299JP-001, TM-638017299KR-001,  
TM-638017299MA-001, TM-638017299PL-001,  
TM-638017299RU-001, TM-638017299SK-001,



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Not Relevant

REACH SVHC

Not Relevant

Halogen-Free

Status

Not Relevant

For more information, please visit [Contact US](#)

China ROHS

Not Relevant

ELV

Not Relevant

RoHS Phthalates

Not Relevant

China RoHS

Search Parts in this Series

207125 Series

Use With

Molex FineAdjust and Mini-Mac Applicators plus the Molex Tape Crimp Module [640162000](#) and most industry standard applicators.

TM-638017299SP-001, TM-638017299TH-001,  
TM-638017299TW-001, TM-638017299VN-001,  
TM-640160065-001, TM-640160065CN-001,  
TM-640160065DE-001, TM-640160065FR-001,  
TM-640160065IT-001, TM-640160065JP-001,  
TM-640160065KR-001, TM-640160065MY-001,  
TM-640160065PL-001, TM-640160065RU-001,  
TM-640160065SK-001, TM-640160065SP-001,  
TM-640160065TH-001, TM-640160065TW-001,  
TM-640160065VN-001, TM-640162000-001,  
TM-640162000SP-001

This document was generated on 12/23/2021

**PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION**

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

## Molex:

[62500-0001](#) [63801-4482](#) [63801-2623](#) [62500-0100](#) [11-31-0691](#) [62200-6003](#) [62500-0020](#) [63801-4463](#) [62200-6023](#)  
[63801-3241](#) [62500-0077](#) [63903-5005](#) [62500-0010](#) [62500-0085](#) [62500-0004](#) [63801-4481](#) [63902-9770](#) [62200-](#)  
[6013](#) [63903-7070](#) [62500-0007](#) [63801-3599](#) [63801-2682](#) [62200-6007](#) [11-31-0692](#) [62200-6021](#) [63903-0152](#) [62500-](#)  
[0055](#) [62500-0015](#) [11-31-0665](#) [63801-2600](#) [63801-2720](#) [62500-0109](#) [63801-9416](#) [63903-0153](#) [11-18-5122](#) [63801-](#)  
[3230](#) [63801-2681](#) [62500-0079](#) [90-20-1330](#) [11-31-0653](#) [62500-0089](#) [62500-0002](#) [63801-4484](#) [62500-0006](#) [62500-](#)  
[0112](#) [63902-9870](#) [62200-6006](#) [63801-9190](#) [62500-0108](#) [62200-6027](#) [62500-0014](#) [63903-9370](#) [62500-0078](#)  
[63801-9414](#) [62500-0101](#) [62500-0022](#) [90-20-0885](#) [63801-4210](#) [63801-2200](#) [63801-3260](#) [19286-0802](#) [62500-0118](#)  
[62800-5121](#) [62200-4604](#) [62200-6004](#) [11-31-0657](#) [63801-9415](#) [11-31-0656](#) [62500-0051](#) [62200-6024](#) [11-31-0666](#)  
[62200-6010](#) [62500-0094](#) [63801-4483](#) [66722-8500](#) [63903-6870](#) [63801-2680](#) [62500-0021](#) [62200-6014](#) [63903-9470](#)  
[62500-0093](#) [62500-0050](#) [11-31-0635](#) [62201-7590](#) [62500-0087](#) [62200-5614](#) [62800-1135](#) [19286-0600](#) [62200-5607](#)  
[62500-0023](#) [63801-9234](#) [11-31-0652](#) [62500-0115](#) [62500-0091](#) [62200-6002](#) [62500-0075](#) [62500-0096](#) [63903-0151](#)  
[62200-6016](#) [62200-6012](#)