

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0638131400

Status:

Active

Overview:

Application Tooling

Description:

Extraction Tool for SPOX, MX64, Ditto, MX150CE, Milli-Grid Terminals

Documents:

RoHS Certificate of Compliance (PDF)

General	
Product Family	Application Tooling
Series	207121
Comments	See Tooling Specification (PDF) Above
Function	Extraction
Geographic Area	Global
Level of Automation	Manual
More Detailed Tech Information	applicationtooling@molex.com
Overview	Application Tooling
Product Name	N/A
Tool Type	Extraction Hand Tool
UPC	756054688069
Warranty Disclaimer	CAUTION: Molex tooling crimp specifications are valid only when used with Molex terminals and tooling manufactured by Molex and sold by Molex or authorized distributors ("Molex Tooling"). When using tooling other than Molex Tooling with Molex specific connector systems listed in our ATS documents, the Molex tooling qualification does not apply and the responsibility for full qualification of the connector system is that of the customer. Molex accepts no liability for connector performance or tooling support where tooling other than Molex Tooling is used or where Molex Tooling is modified.

Material Info

Reference - Drawing Numbers

Application Tooling Documents

ATS-638131400-001, TM-638000029-001, TM-638000029CN-001, TM-638000029DE-001, TM-638000029FR-001, TM-638000029IT-001, TM-638000029JP-001, TM-638000029KR-001, TM-638000029MY-001, TM-638000029PL-001, TM-638000029RU-001, TM-638000029SK-001, TM-638000029SP-001, TM-638000029TH-001, TM-638000029TW-001, TM-638000029VN-001



Series image - Reference only

EU ELV	
Not Relevant	
EU RoHS	China RoHS
Not Reviewed	
REACH SVHC	
Not Reviewed	
Halogen-Free	
Status	
Not Relevant	
For more information, please visit Contact US	
China ROHS	Not Relevant
ELV	Not Relevant
RoHS Phthalates	Not Reviewed

Search Parts in this Series

207121 Series

Application Tooling Description	FAQ Product #
2.50mm Pitch, Mini-SPOX Female Crimp Terminal, 22-28 AWG, Reel	8701039
Ditto Hermaphroditic Crimp Terminal, Tin Brass, Preplated Tin, 20-22 AWG	1502000001
Ditto Hermaphroditic Crimp Terminal, Tin Brass, Preplated Tin, 24-26 AWG	1502000002
Ditto Hermaphroditic Crimp Terminal, Copper Nickel, Select Gold Plating, 20-22 AWG, for High-Temperature (-40° to +150°C) Housing	1502000011
Ditto Hermaphroditic Crimp Terminal,	1502000012

Copper Nickel,
Select Gold Plating,
24-26 AWG, for
High-Temperature
(-40° to +150°C)
Housing

2.54mm Pitch MX64 334670003

Terminal, Gold
(Au) Plating, 22
AWG, Right Reel
Payoff, Also used
with MX123 Female
Receptacle Housing

2.54mm Pitch MX64 334670004

Terminal, Gold
(Au) Plating, 22
AWG, Left Reel
Payoff, Also used
with MX123 Female
Receptacle Housing

2.54mm Pitch MX64 334670005

Terminal, Gold
(Au) Plating, 18-20
AWG, Right Reel
Payoff, Also used
with MX123 Female
Receptacle Housing

2.54mm Pitch MX64 334670006

Terminal, Gold
(Au) Plating, 18-20
AWG, Left Reel
Payoff, Also used
with MX123 Female
Receptacle Housing

2.54mm Pitch MX64 334680001

Terminal, Tin (Sn)
Plating, 22 AWG,
Right Reel Payoff,
Also used with
MX123 Female
Receptacle Housing

2.54mm Pitch MX64 334680002

Terminal, Tin (Sn)
Plating, 22 AWG,
Left Reel Payoff,
Also used with
MX123 Female
Receptacle Housing

2.54mm Pitch MX64 334680003

Terminal, Tin (Sn)
Plating, 18-20 AWG,
Right Reel Payoff,
Also used with
MX123 Female
Receptacle Housing

2.54mm Pitch MX64 334680004

Terminal, Tin (Sn)
Plating, 18-20 AWG,
Left Reel Payoff,
Also used with
MX123 Female
Receptacle Housing

2.54mm Pitch MX64 334680022

Terminal, Tin (Sn)
Plating, 0.35mm²

Wire, Right Reel
Payoff, Also used
with MX123 Female
Receptacle Housing
2.54mm Pitch 334680023
MX64 Terminal,
Tin (Sn) Plating,
0.50-0.75mm² Wire,
Left Reel Payoff,
Also used with
MX123 Female
Receptacle Housing
2.54mm Pitch 334680024
MX64 Terminal,
Tin (Sn) Plating,
0.50-0.75mm²
Wire, Right Reel
Payoff, Also used
with MX123 Female
Receptacle Housing
Ditto Hermaphroditic 368760001
Crimp Terminal, High
Copper, Tin Plating,
20-22 AWG
Ditto Hermaphroditic 368760002
Crimp Terminal, High
Copper, Tin Plating,
24-26 AWG
2.00mm Pitch, Milli- 503948051
Grid Female Crimp
Terminal, 0.38μm
Select Gold, Reel,
Lead free
2.00mm Pitch, Milli- 503948052
Grid Female Crimp
Terminal, 0.76μm
Select Gold, Reel,
Lead-Free
2.00mm Pitch, Milli- 503948054
Grid Female Crimp
Terminal, Gold (Au)
Flash, Reel, Lead
free
2.00mm Pitch, Milli- 503948055
Grid Female Crimp
Terminal, Matte Tin
Plating, Reel, Lead
free
2.00mm Pitch, Milli- 503948100
Grid Female Crimp
Terminal, 0.38μm
Select Gold Plating,
Bag, Lead free
2.00mm Pitch, Milli- 503948200
Grid Female Crimp
Terminal, 0.76μm
Select Gold Plating,
Bag, Lead free
2.00mm Pitch, Milli- 503948400
Grid Female Crimp
Terminal, Gold Flash
Plating, Bag, Lead
free

This document was generated on 10/07/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[63813-1400](#)