

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0638137000

Status:

Active

Overview:

Application Tooling


Description:

Extractor Tool for 2.80mm Crimp Terminals

Documents:

RoHS Certificate of Compliance (PDF)

General	
Product Family	Application Tooling
Series	207121
Comments	See Tooling Specification (PDF) Above
Function	Extraction
Geographic Area	Global
Level of Automation	Manual
More Detailed Tech Information	applicationtooling@molex.com
Overview	Application Tooling
Product Name	N/A
Tool Type	Extraction Hand Tool
UPC	884982141445
Warranty Disclaimer	CAUTION: Molex tooling crimp specifications are valid only when used with Molex terminals and tooling manufactured by Molex and sold by Molex or authorized distributors ("Molex Tooling"). When using tooling other than Molex Tooling with Molex specific connector systems listed in our ATS documents, the Molex tooling qualification does not apply and the responsibility for full qualification of the connector system is that of the customer. Molex accepts no liability for connector performance or tooling support where tooling other than Molex Tooling is used or where Molex Tooling is modified.
Material Info	
Reference - Drawing Numbers	
Application Tooling Documents	ATS-638137000-001



EU ELV	
Not Reviewed	
EU RoHS	China RoHS
Not Reviewed	
REACH SVHC	
Not Reviewed	
Halogen-Free	
Status	
Not Reviewed	
For more information, please visit Contact US	
China ROHS	Not Reviewed
ELV	Not Reviewed
RoHS Phthalates	Not Reviewed

Search Parts in this Series

207121 Series

Use With

98658 MOX Crimp Terminal, Female, 0.635mm Crimp Terminal in 2.54mm MOX Receptacle Housing with TPA Dual Row, 1x 6 Circuits.

Application Tooling Description	FAQ Product #
2.85mm Pitch MOX Receptacle Housing with TPA, Single Row, 6 Circuits, Black	981930001
MOX Crimp Terminal, Female, 0.635mm, 20-24 AWG (0.22-0.60mm²), Reel, Tin (Sn)	986581211
MOX Crimp Terminal, Female, 0.635mm, 18-22 AWG (0.75mm²), Reel, Tin (Sn)	986581212

	MOX Crimp	<u>986581213</u>
	Terminal, Female,	
	0.635mm,	
	20-24 AWG	
	(0.22-0.50mm²),	
	Reel, Tin (Sn)	
	MOX Crimp	<u>986581221</u>
	Terminal, Female,	
	0.635mm,	
	20-24 AWG	
	(0.22-0.60mm²),	
	Reel, Selective Gold	
	MOX Crimp	<u>986581222</u>
	Terminal, Female,	
	0.635mm, 18-22	
	AWG (0.75mm²),	
	Reel, Selective Gold	
	MOX Crimp	<u>986581223</u>
	Terminal, Female,	
	0.635mm,	
	20-24 AWG	
	(0.22-0.50mm²),	
	Reel, Selective Gold	
	MOX Crimp	<u>986581231</u>
	Terminal, Female,	
	0.635mm,	
	20-24 AWG	
	(0.22-0.60mm²),	
	Reel, 2 Points	
	Selective Gold	
	MOX Crimp	<u>986581232</u>
	Terminal, Female,	
	0.635mm, 18-22	
	AWG (0.75mm²),	
	Reel, 2 Points	
	Selective Gold	
	MOX Crimp	<u>986581233</u>
	Terminal, Female,	
	0.635mm,	
	20-24 AWG	
	(0.22-0.50mm²),	
	Reel, 2 Points	
	Selective Gold	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[63813-7000](#)