

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0638192900

Status:

Active

Overview:

Application Tooling

Description:

PremiumGrade Hand Crimp Tool for Low Force Micro-Fit 3.0 Terminals, 20-30 AWG

Documents:

RoHS Certificate of Compliance (PDF)

General

Product Family

Series

Comments

Function

Geographic Area

Level of Automation

More Detailed Tech Information

Overview

Product Name

Tool Type

UPC

Warranty Disclaimer

Application Tooling

207129

See Tooling Specification (PDF) Above. Type: 4D Crimp

Global

Manual

applicationtooling@molex.com

Application Tooling

PremiumGrade

Hand Crimp Tool

883906601218

CAUTION: Molex tooling crimp specifications are valid only when used with Molex terminals and tooling manufactured by Molex and sold by Molex or authorized distributors ("Molex Tooling"). When using tooling other than Molex Tooling with Molex specific connector systems listed in our ATS documents, the Molex tooling qualification does not apply and the responsibility for full qualification of the connector system is that of the customer. Molex accepts no liability for connector performance or tooling support where tooling other than Molex Tooling is used or where Molex Tooling is modified.

Physical

Net Weight

317.100/g

Material Info

Reference - Drawing Numbers

Application Tooling Documents

ATS-638192900-001, TM-638000029-001, TM-638000029CN-001, TM-638000029DE-001, TM-638000029FR-001, TM-638000029IT-001, TM-638000029JP-001, TM-638000029KR-001, TM-638000029MY-001, TM-638000029PL-001, TM-638000029RU-001, TM-638000029SK-001, TM-638000029SP-001, TM-638000029TH-001, TM-638000029TW-001, TM-638000029VN-001



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Not Reviewed

REACH SVHC

Not Contained Per - ED/61/2018 (27 June 2018)

Halogen-Free Status

Not Relevant

For more information, please visit [Contact US](#)

China RoHS

Not Relevant

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

207129 Series

Use With

46235 Micro-Fit 3.0 Crimp Terminals

Application Tooling Description	FAQ Product #
Micro-Fit RMF Reduced Mating Force, Crimp Terminal, Female, with 0.38µm Selective Gold (Au) over Nickel (Ni), 20-24 AWG, without Lubricant	462350001
Micro-Fit RMF Reduced Mating Force, Crimp Terminal, Female, with 0.76µm Selective Gold (Au) over Nickel (Ni),	462350002

20-24 AWG, without Lubricant	
Micro-Fit RMF	<u>462350003</u>
Reduced Mating Force, Crimp Terminal, Female, with 0.38µm	
Selective Gold (Au) over Nickel (Ni),	
26-30 AWG, without Lubricant	
Micro-Fit RMF	<u>462350004</u>
Reduced Mating Force, Crimp Terminal, Female, with .0.76µm	
Selective Gold (Au) over Nickel (Ni),	
26-30 AWG, without Lubricant	
Micro-Fit RMF	<u>462355001</u>
High Mating Cycle, Reduced Mating Force, Crimp Terminal, Female, with 0.38µm	
Selective Gold (Au) over Nickel (Ni),	
20-24 AWG, with Lubricant	
Micro-Fit RMF	<u>462355002</u>
High Mating Cycle, Reduced Mating Force, Crimp Terminal, Female, with 0.76µm	
Selective Gold (Au) over Nickel (Ni),	
20-24 AWG, with Lubricant	
Micro-Fit RMF	<u>462355003</u>
High Mating Cycle, Reduced Mating Force, Crimp Terminal, Female, with 0.38µm	
Selective Gold (Au) over Nickel (Ni),	
26-30 AWG, with Lubricant	
Micro-Fit RMF	<u>462355004</u>
High Mating Cycle, Reduced Mating Force, Crimp Terminal, Female, with .0.76µm	
Selective Gold (Au) over Nickel (Ni),	
26-30 AWG, with Lubricant	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

63819-2900