

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0638258400

Status:

Active

Overview:

Application Tooling

Description:

Hand Tool for MX64 ISO Terminal

Documents:

RoHS Certificate of Compliance (PDF)

General	
Product Family	Application Tooling
Series	207129
Comments	Die sets are not sold separately; the complete hand tool needs to be ordered to obtain the die set. Type: 4A
Function	Crimp
Geographic Area	Global
Level of Automation	Manual
More Detailed Tech Information	<a href="mailto:applicationtooling@molex.com">applicationtooling@molex.com</a>
Overview	Application Tooling
Product Name	PremiumGrade
Tool Type	Hand Crimp Tool
UPC	887191247755
Warranty Disclaimer	CAUTION: Molex tooling crimp specifications are valid only when used with Molex terminals and tooling manufactured by Molex and sold by Molex or authorized distributors ("Molex Tooling"). When using tooling other than Molex Tooling with Molex specific connector systems listed in our ATS documents, the Molex tooling qualification does not apply and the responsibility for full qualification of the connector system is that of the customer. Molex accepts no liability for connector performance or tooling support where tooling other than Molex Tooling is used or where Molex Tooling is modified.

Material Info

Reference - Drawing Numbers

Application Tooling Documents

ATS-6382584HM-001, TM-638000029-001



Series image - Reference only

EU ELV	
Not Relevant	
EU RoHS	China RoHS
Compliant	
REACH SVHC	
Not Reviewed	
Halogen-Free	
Status	
Not Relevant	
For more information, please visit <a href="#">Contact US</a>	
China ROHS	Not Relevant
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

207129 Series

Use With

33467 , 33468 , 34736 MX64 ISO Terminal, 0.35mm2 and 0.50-0.75mm2 wire

Application Tooling Description	FAQ Product #
2.54mm Pitch MX64 Terminal, Gold (Au) Plating, 0.35mm2 Wire, Left ReelPayoff, Also used with MX123 Female Receptacle Housing	<a href="#">334670021</a>
2.54mm Pitch MX64 Terminal, Gold (Au) Plating, 0.35mm2 Wire, Right Reel Payoff, Also used with MX123 Female Receptacle Housing	<a href="#">334670022</a>
2.54mm Pitch MX64 Terminal, Gold (Au) Plating,	<a href="#">334670023</a>

0.50-0.75mm<sup>2</sup> Wire,  
Left Reel Payoff,  
Also used with  
MX123 Female  
Receptacle Housing  
2.54mm Pitch 334670024  
MX64 Terminal,  
Gold (Au) Plating,  
0.50-0.75mm<sup>2</sup>  
Wire, Right Reel  
Payoff, Also used  
with MX123 Female  
Receptacle Housing  
2.54mm Pitch MX64 334680021  
Terminal, Tin (Sn)  
Plating, 0.35mm<sup>2</sup>  
Wire, Left Reel  
Payoff, Also used  
with MX123 Female  
Receptacle Housing  
2.54mm Pitch MX64 334680022  
Terminal, Tin (Sn)  
Plating, 0.35mm<sup>2</sup>  
Wire, Right Reel  
Payoff, Also used  
with MX123 Female  
Receptacle Housing  
2.54mm Pitch 334680023  
MX64 Terminal,  
Tin (Sn) Plating,  
0.50-0.75mm<sup>2</sup> Wire,  
Left Reel Payoff,  
Also used with  
MX123 Female  
Receptacle Housing  
2.54mm Pitch 334680024  
MX64 Terminal,  
Tin (Sn) Plating,  
0.50-0.75mm<sup>2</sup>  
Wire, Right Reel  
Payoff, Also used  
with MX123 Female  
Receptacle Housing  
2.54mm Pitch MX64 347360025  
Terminal, Silver  
Plating, 0.35mm<sup>2</sup>,  
Left Reel Payoff,  
Also used with  
MX123 Female  
Receptacle Housing  
2.54mm Pitch MX64 347360026  
Terminal, Silver  
Plating, 0.35mm<sup>2</sup>,  
Right Reel Payoff,  
Also used with  
MX123 Female  
Receptacle Housing  
2.54mm Pitch 347360027  
MX64 Terminal,  
Silver Plating,  
0.50-0.75mm<sup>2</sup>, Left  
Reel Payoff, Also  
used with MX123  
Female Receptacle  
Housing

2.54mm Pitch  
MX64 Terminal,  
Silver Plating,  
0.50-0.75mm², Right  
Reel Payoff, Also  
used with MX123  
Female Receptacle  
Housing

347360028

This document was generated on 10/07/2021

**PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION**

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

63825-8400