

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0638276200

Status:

Active

Overview:

Application Tooling

Description:

Hand Tool for Appli-Mate RAST Power Connectors

Documents:

RoHS Certificate of Compliance (PDF)

General	
Product Family	Application Tooling
Series	207129
ApplicationTooling Video	www.youtube.com/watch?v=0rydbPYMfoA
Comments	See Tooling Specification (PDF) Above
Function	Crimp
Geographic Area	Global
Level of Automation	Manual
More Detailed Tech Information	applicationtooling@molex.com
Overview	Application Tooling
Product Name	PremiumGrade
Tool Type	Hand Crimp Tool
UPC	889056010368
Warranty Disclaimer	CAUTION: Molex tooling crimp specifications are valid only when used with Molex terminals and tooling manufactured by Molex and sold by Molex or authorized distributors ("Molex Tooling"). When using tooling other than Molex Tooling with Molex specific connector systems listed in our ATS documents, the Molex tooling qualification does not apply and the responsibility for full qualification of the connector system is that of the customer. Molex accepts no liability for connector performance or tooling support where tooling other than Molex Tooling is used or where Molex Tooling is modified.

Material Info

Reference - Drawing Numbers	
Application Tooling Documents	ATS-6382762HM-001



Series image - Reference only

EU ELV	
Not Relevant	
EU RoHS	China RoHS
Compliant	
REACH SVHC	
Not Reviewed	
Halogen-Free	
Status	
Not Relevant	
For more information, please visit Contact US	
China ROHS	Not Relevant
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

207129 Series

Use With

91627 , 93211 Appli-Mate RAST Power connectors, 2 – 12 circuits, 0.5mm² H05V-K wires . 91791 , 93322 Appli-Mate RAST Power connectors, 2 – 12 circuits, 0.75mm² H05V-K wires

Application Tooling Description	FAQ Product #
5.00mm Pitch Appli-Mate RAST Power IDT Housing, Direct/ Indirect, Female, 2 Circuits, Glow-Wire Capable, Fully Coded, Open End Walls	916270001
5.00mm Pitch Appli-Mate RAST Power IDT Housing, Direct/ Indirect, Female, 3 Circuits, Glow-Wire Capable, Fully	916271001

	Coded, Open End Walls
	5.00mm Pitch Appli- 916272001
	Mate RAST Power
	IDT Housing, Direct/
	Indirect, Female,
	4 Circuits, Glow-
	Wire Capable, Fully
	Coded, Open End Walls
	5.00mm Pitch Appli- 916273001
	Mate RAST Power
	IDT Housing, Direct/
	Indirect, Female,
	5 Circuits, Glow-
	Wire Capable, Fully
	Coded, Open End Walls
	5.00mm Pitch Appli- 916274001
	Mate RAST Power
	IDT Housing, Direct/
	Indirect, Female,
	6 Circuits, Glow-
	Wire Capable, Fully
	Coded, Open End Walls
	5.00mm Pitch Appli- 916275001
	Mate RAST Power
	IDT Housing, Direct/
	Indirect, Female,
	7 Circuits, Glow-
	Wire Capable, Fully
	Coded, Open End Walls
	5.00mm Pitch Appli- 916276001
	Mate RAST Power
	IDT Housing, Direct/
	Indirect, Female,
	8 Circuits, Glow-
	Wire Capable, Fully
	Coded, Open End Walls
	5.00mm Pitch Appli- 916277001
	Mate RAST Power
	IDT Housing, Direct/
	Indirect, Female,
	9 Circuits, Glow-
	Wire Capable, Fully
	Coded, Open End Walls
	5.00mm Pitch Appli- 916278001
	Mate RAST Power
	IDT Housing, Direct/
	Indirect, Female,
	10 Circuits, Glow-
	Wire Capable, Fully
	Coded, Open End Walls
	5.00mm Pitch Appli- 916279001
	Mate RAST Power
	IDT Housing, Direct/
	Indirect, Female,
	11 Circuits, Glow-
	Wire Capable, Fully

Coded, Open End
Walls
5.00mm Pitch Appli- 916279501
Mate RAST Power
IDT Housing, Direct/
Indirect, Female,
12 Circuits, Glow-
Wire Capable, Fully
Coded, Open End
Walls

This document was generated on 10/06/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

63827-6200