

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0638830600](#)
Status: **Active**
Overview: [Application Tooling](#)
Description: [Mini-Mac Applicator](#)

Documents:
[RoHS Certificate of Compliance \(PDF\)](#)

General
Product Family [Application Tooling](#)
Series [207127](#)
Function [Crimp](#)
Geographic Area [Global](#)
Level of Automation [Automatic, Semi-Automatic](#)
More Detailed Tech Information [applicationtooling@molex.com](#)
Overview [Application Tooling](#)
Product Name [Mini-Mac](#)
Tool Type [Applicator](#)
UPC [822348744275](#)
Warranty Disclaimer [CAUTION: Molex tooling crimp specifications are valid only when used with Molex terminals and tooling manufactured by Molex and sold by Molex or authorized distributors \("Molex Tooling"\). When using tooling other than Molex Tooling with Molex specific connector systems listed in our ATS documents, the Molex tooling qualification does not apply and the responsibility for full qualification of the connector system is that of the customer. Molex accepts no liability for connector performance or tooling support where tooling other than Molex Tooling is used or where Molex Tooling is modified.](#)

Physical
Net Weight [4846.612/g](#)

Material Info

Reference - Drawing Numbers
[Application Tooling Documents](#)
[ATS-638830600-001, TM-638800000-001, TM-638800000SP-001, TM-640160065-001, TM-640160065CN-001, TM-640160065DE-001, TM-640160065FR-001, TM-640160065IT-001, TM-640160065JP-001, TM-640160065KR-001, TM-640160065MY-001, TM-640160065PL-001, TM-640160065RU-001, TM-640160065SK-001, TM-640160065SP-001, TM-640160065TH-001, TM-640160065TW-001, TM-640160065VN-001](#)

Series image - Reference only

EU ELV
Not Relevant
EU RoHS **China RoHS**
Not Reviewed
REACH SVHC
Not Reviewed
Halogen-Free
Status
Not Relevant
For more information, please visit [Contact US](#)

China ROHS Not Relevant
ELV Not Relevant
RoHS Phthalates Not Reviewed

Search Parts in this Series
[207127 Series](#)

Use With
Molex TM-3000: [638017200](#) , [638017300](#) , Molex TM-4000: [638017600](#) , Molex TM-2000: [638008300](#) , [638008400](#) , and Most Industry Standard Presses or Wire Process Machines

Application Tooling Description	FAQ Product #
InsulKrimp Quick Disconnect, Female, for 24-26 (0.20-0.12mm²), Continuous Molded Strip, Tab 4.75 x 0.51mm, Yellow	190030103
InsulKrimp Quick Disconnect, Female, for 24-26 (0.20-0.12mm²), Continuous Molded Strip, Tab 4.75 x 0.81mm, Dark Yellow	190030104
InsulKrimp Quick Disconnect, Female, for 24-26 (0.20-0.12mm²), Continuous Molded Strip, Tab 6.35 x 0.81mm, Yellow	190030106
InsulKrimp Quick Disconnect, Female, Continuous Molded Strip, Tab 4.75 x 0.51mm	190030140

InsulKrimp Quick 190030143
Disconnect, Female,
Continuous Molded
Strip, Tab 4.75 x
0.81mm

This document was generated on 07/29/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[63883-0600](#)