

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0638911100

Status:

Active

Overview:

Application Tooling

Description:

Mini-Mac Applicator for Mini-Fit Sr. Male and Female Terminals for 10-12 AWG Wire with Insulation Diameter 4.40-5.30mm

Documents:

RoHS Certificate of Compliance (PDF)

General	
Product Family	Application Tooling
Series	207127
Comments	See Tooling Specification (PDF) Above
Function	Crimp
Geographic Area	Global
Level of Automation	Automatic, Semi-Automatic
More Detailed Tech Information	applicationtooling@molex.com
Overview	Application Tooling
Product Name	Mini-Mac
Tool Type	Applicator
UPC	800756656045
Warranty Disclaimer	CAUTION: Molex tooling crimp specifications are valid only when used with Molex terminals and tooling manufactured by Molex and sold by Molex or authorized distributors ("Molex Tooling"). When using tooling other than Molex Tooling with Molex specific connector systems listed in our ATS documents, the Molex tooling qualification does not apply and the responsibility for full qualification of the connector system is that of the customer. Molex accepts no liability for connector performance or tooling support where tooling other than Molex Tooling is used or where Molex Tooling is modified.
Physical	
Net Weight	4956.386/g
Material Info	
Reference - Drawing Numbers	
Application Tooling Documents	ATS-638911100-001, TM-638000029-001, TM-638000029CN-001, TM-638000029DE-001, TM-638000029FR-001, TM-638000029IT-001, TM-638000029JP-001, TM-638000029KR-001, TM-638000029MY-001, TM-638000029PL-001, TM-638000029RU-001, TM-638000029SK-001, TM-638000029SP-001, TM-638000029TH-001, TM-638000029TW-001, TM-638000029VN-001, TM-638000100-001, TM-638000100SP-001

Series image - Reference only

EU ELV

Product not active

EU RoHS

Product not active

REACH SVHC

Product not active

Halogen-Free Status

Product not active

For more information, please visit [Contact US](#)

China ROHS

Product not active

ELV

Product not active

RoHS Phthalates

Product not active

Search Parts in this Series

207127 Series

Use With

Molex TM-3000: [638017200](#) , [638017300](#) , Molex TM-4000: [638017600](#) , Molex TM-2000: [638008300](#) , [638008400](#) , and Most Industry Standard Presses or Wire Process Machines

Application Tooling | FAQ

Description	Product #
Mini-Fit Sr. Crimp Terminal, Female, 10-12 AWG, Gold (Au)	428150012
Mini-Fit Sr. Crimp Terminal, Female, 10-12 AWG, Silver (Ag)	428150114
Mini-Fit Sr. Crimp Terminal, Male, 10-12 AWG, Gold (Au)	428170012
Mini-Fit Sr. Crimp Terminal, Male, 10-12 AWG, Gold (Au)	428170112
Mini-Fit Sr. Crimp Terminal, Male, 10-12 AWG, Silver (Ag)	428171014
Mini-Fit Sr. Crimp Terminal, Male, 10-12 AWG, Silver (Ag)	428171114

This document was generated on 07/27/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[63891-1100](#)