

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:	<u>0638916000</u>
Status:	Active
Overview:	<u>Application Tooling</u>
Description:	Mini-Mac Applicator

Documents:

[RoHS Certificate of Compliance \(PDF\)](#)

General

General	
Product Family	Application Tooling
Series	<u>207127</u>
Comments	See Tooling Specification (PDF) Above
Function	Crimp
Geographic Area	Global
Level of Automation	Automatic, Semi-Automatic
More Detailed Tech Information	<u>applicationtooling@molex.com</u>
Overview	<u>Application Tooling</u>
Product Name	Mini-Mac
Tool Type	Applicator
UPC	800756656113
Warranty Disclaimer	CAUTION: Molex tooling crimp specifications are valid only when used with Molex terminals and tooling manufactured by Molex and sold by Molex or authorized distributors ("Molex Tooling"). When using tooling other than Molex Tooling with Molex specific connector systems listed in our ATS documents, the Molex tooling qualification does not apply and the responsibility for full qualification of the connector system is that of the customer. Molex accepts no liability for connector performance or tooling support where tooling other than Molex Tooling is used or where Molex Tooling is modified.

Physical

Net Weight	4871.260/g
------------	------------

Material Info

Reference - Drawing Numbers

Application Tooling Documents ATS-638916000-001, TM-638000100-001,
TM-638000100SP-001

Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Relevant

For more information, please visit [Contact US](#)

China RoHS

China ROHS

Not Relevant

ELV

Not Relevant

RoHS Phthalates

Not Reviewed

Search Parts in this Series

207127 Series

Use With

Molex TM-3000: 638017200, 638017300
 , Molex TM-4000: 638017600, Molex
 TM-2000: 638008300, 638008400, and
 Most Industry Standard Presses or Wire
 Process Machines

Application Tooling Description

| **FAO**

Product

Sabre Crimp
Terminal, Female,
14-16 AWG, 0.79mm
max. Insulation
Diameter, Reel
Packaged, Tin (Sn)
Plated Brass Contact
Sabre Single Crimp 433750001
Terminal, Female,
14-16 AWG, 3.30mm
Max. Insulation
Diameter, Reel
Packaged, Tin (Sn)
Plated Brass Contact
with TPA

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[63891-6000](#)