

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: 0638916100		Series image - Reference only	
Status: Active		EU ELV Not Relevant EU RoHS Not Reviewed REACH SVHC Not Reviewed Halogen-Free Status Not Relevant For more information, please visit Contact US China ROHS ELV RoHS Phthalates Not Relevant Not Relevant Not Reviewed	
Overview: Application Tooling			
Description: Mini-Mac Applicator			
Documents: RoHS Certificate of Compliance (PDF)			
General			
Product Family	Application Tooling		
Series	207127		
Comments	<p style="margin-top: 0; margin-bottom: 0">For Standard 4.80mm wide insulation crimp <p style="margin-top: 0; margin-bottom: 0">See Tooling Specification (PDF) Above		
Function	Crimp		
Geographic Area	Global		
Level of Automation	Automatic, Semi-Automatic		
More Detailed Tech Information	applicationtooling@molex.com		
Overview	Application Tooling		
Product Name	Mini-Mac		
Tool Type	Applicator		
UPC	800756656120		
Warranty Disclaimer	CAUTION: Molex tooling crimp specifications are valid only when used with Molex terminals and tooling manufactured by Molex and sold by Molex or authorized distributors ("Molex Tooling"). When using tooling other than Molex Tooling with Molex specific connector systems listed in our ATS documents, the Molex tooling qualification does not apply and the responsibility for full qualification of the connector system is that of the customer. Molex accepts no liability for connector performance or tooling support where tooling other than Molex Tooling is used or where Molex Tooling is modified.		
Physical			
Net Weight	4869.730/g		
Material Info			
Reference - Drawing Numbers			
Application Tooling Documents	ATS-638916100-001, TM-638000100-001, TM-638000100SP-001		

Search Parts in this Series 207127 Series	
Use With Molex TM-3000: 638017200 , 638017300 , Molex TM-4000: 638017600 , Molex TM-2000: 638008300 , 638008400 , and Most Industry Standard Presses or Wire Process Machines	
Application Tooling Description	FAQ Product #
Sabre Double Crimp Terminal, Female, Double 18 AWG, 4.57mm Max. Insulation Diameter, Reel Packaged, Tin (Sn) Plated Brass Contact with TPA	433751001

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

63891-6100