

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0639008300](#)
Status: **Active**
Overview: [Application Tooling](#)
Description: FineAdjust for Male Terminal, 18-24 AWG Wire

Documents:
[RoHS Certificate of Compliance \(PDF\)](#)

General
Product Family Application Tooling
Series [207127](#)
Comments See Tooling Specification (PDF) Above
Function Crimp
Geographic Area Global
Level of Automation Automatic, Semi-Automatic
More Detailed Tech Information applicationtooling@molex.com
Overview [Application Tooling](#)
Product Name FineAdjust
Tool Type Applicator
UPC 884982003446
Warranty Disclaimer CAUTION: Molex tooling crimp specifications are valid only when used with Molex terminals and tooling manufactured by Molex and sold by Molex or authorized distributors ("Molex Tooling"). When using tooling other than Molex Tooling with Molex specific connector systems listed in our ATS documents, the Molex tooling qualification does not apply and the responsibility for full qualification of the connector system is that of the customer. Molex accepts no liability for connector performance or tooling support where tooling other than Molex Tooling is used or where Molex Tooling is modified.

Physical
Net Weight 5011.049/g

Material Info

Reference - Drawing Numbers
Application Tooling Documents
ATS-639008300-001, TM-638000029-001, TM-638000029CN-001, TM-638000029DE-001, TM-638000029FR-001, TM-638000029IT-001, TM-638000029JP-001, TM-638000029KR-001, TM-638000029MY-001, TM-638000029PL-001, TM-638000029RU-001, TM-638000029SK-001, TM-638000029SP-001, TM-638000029TH-001, TM-638000029TW-001, TM-638000029VN-001, TM-638004900-001, TM-638004900CN-001, TM-638004900DE-001, TM-638004900FR-001, TM-638004900IT-001, TM-638004900JP-001, TM-638004900KR-001, TM-638004900MY-001, TM-638004900PL-001, TM-638004900RU-001, TM-638004900SK-001, TM-638004900SP-001, TM-638004900TH-001, TM-638004900TW-001, TM-638004900VN-001



Series image - Reference only

EU ELV
Not Relevant

EU RoHS	China RoHS
Not Reviewed	
REACH SVHC	
Not Reviewed	
Halogen-Free	
Status	
Not Relevant	
For more information, please visit Contact US	
China ROHS	Not Relevant
ELV	Not Relevant
RoHS Phthalates	Not Reviewed

Search Parts in this Series
[207127](#) Series

Use With
Molex TM-3000: [638017200](#) , [638017300](#) , Molex TM-4000: [638017600](#) , Molex TM-2000: [638008300](#) , [638008400](#) , and Most Industry Standard Presses or Wire Process Machines

Application Tooling Description	FAQ Product #
MX150L Male Terminal for 18-22 AWG Wire, Metal Strip Carrier, Length 25.40mm	194170024
MX150L Male Terminal for 18-22 AWG Wire, Metal Strip Carrier, Length 25.40mm , Gold Plated	194170026
MX150L Male Terminal for 18-22 AWG Wire, Metal	194170028

Strip Carrier, Length
26.16mm
MX150L Male 194170030
Terminal for 18-22
AWG Wire, Length
26.16mm , Metal
Strip Carrier, Gold
Plated

This document was generated on 07/31/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

63900-8300