

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0639020200

Status:

Active

Overview:

Application Tooling

Description:

FineAdjust Applicator for Insulation OD 1.10-1.30mm - 22-28 AWG

Documents:

RoHS Certificate of Compliance (PDF)

General

Product Family

Series

Comments

Function

Geographic Area

Level of Automation

More Detailed Tech Information

Overview

Product Name

Tool Type

UPC

Warranty Disclaimer

Application Tooling

207127

See Tooling Specification (PDF) Above

Crimp

Global

Automatic, Semi-Automatic

applicationtooling@molex.com

Application Tooling

FineAdjust

Applicator

884982271968

CAUTION: Molex tooling crimp specifications are valid only when used with Molex terminals and tooling manufactured by Molex and sold by Molex or authorized distributors ("Molex Tooling"). When using tooling other than Molex Tooling with Molex specific connector systems listed in our ATS documents, the Molex tooling qualification does not apply and the responsibility for full qualification of the connector system is that of the customer. Molex accepts no liability for connector performance or tooling support where tooling other than Molex Tooling is used or where Molex Tooling is modified.

Physical

Net Weight

4984.306/g

Material Info

Reference - Drawing Numbers

Application Tooling Documents

ATS-639020200-001, TM-638000029-001, TM-638000029CN-001, TM-638000029DE-001, TM-638000029FR-001, TM-638000029IT-001, TM-638000029JP-001, TM-638000029KR-001, TM-638000029MY-001, TM-638000029PL-001, TM-638000029RU-001, TM-638000029SK-001, TM-638000029SP-001, TM-638000029TH-001, TM-638000029TW-001, TM-638000029VN-001, TM-638004900-001, TM-638004900CN-001, TM-638004900SP-001



Series image - Reference only

EU ELV	
Not Relevant	
EU RoHS	China RoHS
Not Reviewed	
REACH SVHC	
Not Reviewed	
Halogen-Free	
Status	
Not Relevant	
For more information, please visit Contact US	
China ROHS	Not Relevant
ELV	Not Relevant
RoHS Phthalates	Not Reviewed

Search Parts in this Series

207127 Series

Use With

Molex TM-3000: 638017200 , 638017300 , Molex TM-4000: 638017600 , Molex TM-2000: 638008300 , 638008400 , and Most Industry Standard Presses or Wire Process Machines

Application Tooling Description	FAQ Product #
Mini-Fit Female Crimp Terminal, Tin (Sn) over Copper (Cu) Plated Brass, 22-28 AWG, Reel	39000046
Mini-Fit Male Crimp Terminal, Tin (Sn) over Plated Brass Contact, 22-28 AWG, Reel	39000048
Mini-Fit Female Crimp Terminal, Tin (Sn) over Phosphor Bronze, 22-28 AWG, Reel	39000065

Mini-Fit Male Crimp Terminal, Tin (Sn) over Phosphor Bronze, 22-28 AWG, Reel	<u>39000067</u>
Mini-Fit Male Crimp Terminal, Tin (Sn), Brass, 22-28 AWG, Reel	<u>39000122</u>
Mini-Fit Male Crimp Terminal, Tin (Sn), Phosphor Bronze, 22-28 AWG, Reel	<u>39000128</u>
Mini-Fit Female Crimp Terminal, Selective Gold (Au) and Selective Tin (Sn) over Nickel (Ni), 22-28 AWG, Reel	<u>39000139</u>
Mini-Fit Male Crimp Terminal, Brass, Gold (Au) Contact Plating, Lead-free, 22-28 AWG, Reel	<u>39000145</u>
Mini-Fit Female Crimp Terminal, Selective Gold (Au) over Phosphor Bronze, 22-28 AWG, Reel	<u>39000183</u>
Mini-Fit Female Crimp Terminal, Tin (Sn) over Nickel (Ni), 22-28 AWG, Reel	<u>39000209</u>
Mini-Fit Female Crimp Terminal, Tin (Sn) over Phosphor Bronze, 22-28 AWG, Reel	<u>39000215</u>
Mini-Fit Male Crimp Terminal, Phosphor Bronze, Gold (Au), 22-28 AWG, Reel	<u>39000221</u>
Mini-Fit Male Crimp Terminal, Brass, Gold (Au) Contact Plating, Lead-free, 22-28 AWG, Reel	<u>39000432</u>
Mini-Fit Female Crimp Terminal, Selective Gold (Au) and Selective Tin (Sn) over Nickel (Ni), 22-28 AWG, Reel	<u>39000434</u>
Mini-Fit Plus High Mating Cycle Female Crimp Terminal, 22-24 AWG, Reel, Select Gold (Au) Plating with Proprietary Molex Advanced Contact Surface Finish (CSF) in Contact Area	<u>460182541</u>

This document was generated on 07/27/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

63902-0200