

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0639021900

Status:

Active

Overview:

Application Tooling

Description:

FineAdjust Applicator for 0.60mm CP Terminals, for 0.22mm², 0.35mm², 0.50mm² Metric Wires

Documents:

RoHS Certificate of Compliance (PDF)

General	
Product Family	Application Tooling
Series	207127
Comments	See Tooling Specification (PDF) Above, Terminals the thin wall small insulation with the TXL type American wire and the IR or ID type Metric wires
Function	Crimp
Geographic Area	Global
Level of Automation	Automatic, Semi-Automatic
More Detailed Tech Information	applicationtooling@molex.com
Overview	Application Tooling
Product Name	FineAdjust
Tool Type	Applicator
UPC	884982368200
Warranty Disclaimer	CAUTION: Molex tooling crimp specifications are valid only when used with Molex terminals and tooling manufactured by Molex and sold by Molex or authorized distributors ("Molex Tooling"). When using tooling other than Molex Tooling with Molex specific connector systems listed in our ATS documents, the Molex tooling qualification does not apply and the responsibility for full qualification of the connector system is that of the customer. Molex accepts no liability for connector performance or tooling support where tooling other than Molex Tooling is used or where Molex Tooling is modified.
Physical	
Net Weight	4996.577/g

Material Info

Reference - Drawing Numbers

Application Tooling Documents

ATS-639021900-001, TM-638000029-001, TM-638000029CN-001, TM-638000029DE-001, TM-638000029FR-001, TM-638000029IT-001, TM-638000029JP-001, TM-638000029KR-001, TM-638000029MY-001, TM-638000029PL-001, TM-638000029RU-001, TM-638000029SK-001, TM-638000029SP-001, TM-638000029TH-001, TM-638000029TW-001, TM-638000029VN-001, TM-638004900-001, TM-638004900CN-001, TM-638004900DE-001, TM-638004900FR-001, TM-638004900IT-001, TM-638004900JP-001, TM-638004900KR-001, TM-638004900MY-001, TM-638004900PL-001, TM-638004900RU-001, TM-638004900SK-001, TM-638004900SP-001,



Series image - Reference only

EU ELV	
Not Relevant	
EU RoHS	China RoHS
Not Reviewed	
REACH SVHC	
Not Reviewed	
Halogen-Free	
Status	
Not Relevant	
For more information, please visit Contact US	
China ROHS	Not Relevant
ELV	Not Relevant
RoHS Phthalates	Not Reviewed

Search Parts in this Series

207127 Series

Use With

Molex TM-3000: [638017200](#) , [638017300](#) , Molex TM-4000: [638017600](#) , Molex TM-2000: [638008300](#) , [638008400](#) , and Most Industry Standard Presses or Wire Process Machines

Application Tooling Description	FAQ Product #
0.635mm CMC CP Female Terminal, Tin Plated, for Square 0.6mm x 0.6mm Pins, Wire Size 0.35mm²	643221019
0.635mm CMC CP Female Terminal, Tin Plated, for Square 0.6mm x 0.6mm Pins, Wire Size 0.5mm²	643221039
0.635mm CMC CP Female Terminal, Tin Plated, Selective	643221229

TM-638004900TH-001, TM-638004900TW-001,
TM-638004900VN-001

1.27µm Gold in
Contact Area, for
Square 0.6mm x
0.6mm Pins, Wire
Size 0.35mm²
0.635mm CMC CP [643221239](#)
Female Terminal,
Tin Plated, Selective
1.27µm Gold in
Contact Area, for
Square 0.6mm x
0.6mm Pins, Wire
Size 0.5mm²
0.635mm CMC CP [643221349](#)
Female Terminal,
HP VERSION, Tin
Plated, Selective
1.27µm Gold in
Contact Area, for
Square 0.6mm x
0.6mm Pins, Wire
Size 0.35mm²
0.635mm CMC CP [643221359](#)
Female Terminal,
HP VERSION, Tin
Plated, Selective
1.27µm Gold in
Contact Area, for
Square 0.6mm x
0.6mm Pins, Wire
Size 0.5mm²

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[63902-1900](#)