

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0639024900](#)
Status: **Active**
Overview: [Application Tooling](#)
Description: FineAdjust Applicator for Insulation OD 2.30-2.60mm - 18-24 AWG

Documents:
[RoHS Certificate of Compliance \(PDF\)](#)

General	
Product Family	Application Tooling
Series	207127
Comments	See Tooling Specification (PDF) Above
Function	Crimp
Geographic Area	Global
Level of Automation	Automatic, Semi-Automatic
More Detailed Tech Information	applicationtooling@molex.com
Overview	Application Tooling
Product Name	FineAdjust
Tool Type	Applicator
UPC	884982706590
Warranty Disclaimer	CAUTION: Molex tooling crimp specifications are valid only when used with Molex terminals and tooling manufactured by Molex and sold by Molex or authorized distributors ("Molex Tooling"). When using tooling other than Molex Tooling with Molex specific connector systems listed in our ATS documents, the Molex tooling qualification does not apply and the responsibility for full qualification of the connector system is that of the customer. Molex accepts no liability for connector performance or tooling support where tooling other than Molex Tooling is used or where Molex Tooling is modified.

Physical	
Net Weight	4985.196/g

Material Info

Reference - Drawing Numbers	
Application Tooling Documents	ATS-639024900-001, TM-638000029-001, TM-638000029CN-001, TM-638000029DE-001, TM-638000029FR-001, TM-638000029IT-001, TM-638000029JP-001, TM-638000029KR-001, TM-638000029MY-001, TM-638000029PL-001, TM-638000029RU-001, TM-638000029SK-001, TM-638000029SP-001, TM-638000029TH-001, TM-638000029TW-001, TM-638000029VN-001, TM-638004900-001, TM-638004900CN-001, TM-638004900DE-001, TM-638004900FR-001, TM-638004900IT-001, TM-638004900JP-001, TM-638004900MY-001, TM-638004900PL-001, TM-638004900RU-001, TM-638004900SK-001, TM-638004900SP-001, TM-638004900TH-001, TM-638004900VN-001



Series image - Reference only

EU ELV Not Relevant	
EU RoHS Not Reviewed REACH SVHC Not Reviewed Halogen-Free Status Not Relevant	China RoHS
For more information, please visit Contact US	
China ROHS	Not Relevant
ELV	Not Relevant
RoHS Phthalates	Not Reviewed

Search Parts in this Series
[207127](#) Series

Use With
Molex TM-3000: [638017200](#) , [638017300](#) , Molex TM-4000: [638017600](#) , Molex TM-2000: [638008300](#) , [638008400](#) , and Most Industry Standard Presses or Wire Process Machines

Application Tooling Description	FAQ Product #
Mini-Fit Jr. Grounding Pin, 18-24 AWG, Reel, Phosphor Bronze, Tin or Select Gold (Au)	304901002
Mini-Fit Jr. Crimp Grounding Terminal, Male, with Tin (Sn) Plated Phosphor Bronze Contact, 18-24 AWG, Reel	304902002
Mini-Fit Female Crimp Terminal, Tin (Sn) over Copper	39000038

(Cu) Plated Brass, 18-24, 22+22 AWG, Reel	
Mini-Fit Male Crimp Terminal, Tin (Sn) over Copper (Cu) Plated Brass Contact, 18-24, 22+22 AWG, Reel	<u>39000040</u>
Mini-Fit Female Crimp Terminal, Tin (Sn) over Phosphor Bronze, 18-24, 22 +22 AWG, Reel	<u>39000059</u>
Mini-Fit Male Crimp Terminal, Tin (Sn) over Phosphor Bronze, 18-24, 22+22 AWG, Reel	<u>39000061</u>
Mini-Fit Female Crimp Terminal, Selective Gold (Au) and Selective Tin (Sn) over Nickel (Ni), 18-24 AWG, Reel	<u>39000073</u>
Mini-Fit Male Crimp Terminal, Brass, Gold (Au) Contact Plating, Lead-free, 18-24 AWG, Reel	<u>39000075</u>
Mini-Fit Male Crimp Terminal, Tin (Sn) Plated Brass Contact, 18-24 AWG, Reel	<u>39000120</u>
Mini-Fit Male Crimp Terminal, Tin (Sn) Plated Brass Contact, 18-24 AWG, Bag	<u>39000121</u>
Mini-Fit Male Crimp Terminal, Tin (Sn), Phosphor Bronze, 18-24 AWG, Reel	<u>39000126</u>
Mini-Fit Female Crimp Terminal, Selective Gold (Au) over Phosphor Bronze, 18-24 AWG, Reel	<u>39000181</u>
Mini-Fit Female Crimp Terminal, Tin (Sn) over Nickel (Ni), 18-24 AWG, Reel	<u>39000207</u>
Mini-Fit Female Crimp Terminal, Tin (Sn) over Phosphor Bronze, 18-24 AWG, Reel	<u>39000213</u>
Mini-Fit Male Crimp Terminal, Phosphor Bronze, Gold (Au), 18-24 AWG, Reel	<u>39000219</u>
Mini-Fit Female Crimp Terminal,	<u>39000428</u>

Selective Gold (Au)
and Selective Tin
(Sn) over Nickel (Ni),
18-24 AWG, Reel
Mini-Fit Male Crimp 39000430
Terminal, Brass,
Gold (Au) Contact
Plating, Lead-free,
18-24 AWG, Reel
Mini-Fit Plus Crimp 457501111
Terminal, 18-20
AWG, Reel, Copper
(Cu) Alloy, Tin (Sn)
Mini-Fit Plus Crimp 457501211
Terminal, 18-20
AWG, Reel, Copper
(Cu) Alloy, Gold (Au)
Selective
Mini-Fit Plus Crimp 460121141
Terminal, 18-20
AWG, Reel, Tin (Sn)
Plating
Mini-Fit Plus Crimp 460121241
Terminal, 18-20
AWG, Reel, 0.76µm
Selective Gold (Au)
Plating
Mini-Fit Plus High 460181541
Mating Cycle Female
Crimp Terminal,
18-20 AWG,
Reel, Select Gold
(Au) Plating with
Proprietary Molex
Advanced Contact
Surface Finish (CSF)
in Contact Area

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[63902-4900](#)