

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0639025100

Status:

Active

Overview:

Application Tooling

Description:

FineAdjust Applicator for MX64 ISO Terminal

Documents:

RoHS Certificate of Compliance (PDF)

General	
Product Family	Application Tooling
Series	207127
Comments	See Tooling Specification (PDF) Above
Function	Crimp
Geographic Area	Global
Level of Automation	Automatic, Semi-Automatic
More Detailed Tech Information	applicationtooling@molex.com
Overview	Application Tooling
Product Name	FineAdjust
Tool Type	Applicator
UPC	884982945074
Warranty Disclaimer	CAUTION: Molex tooling crimp specifications are valid only when used with Molex terminals and tooling manufactured by Molex and sold by Molex or authorized distributors ("Molex Tooling"). When using tooling other than Molex Tooling with Molex specific connector systems listed in our ATS documents, the Molex tooling qualification does not apply and the responsibility for full qualification of the connector system is that of the customer. Molex accepts no liability for connector performance or tooling support where tooling other than Molex Tooling is used or where Molex Tooling is modified.

Physical	
Net Weight	5052.033/g

Material Info

Reference - Drawing Numbers	
Application Tooling Documents	ATS-639025100-001, TM-638000029-001, TM-638000029CN-001, TM-638000029DE-001, TM-638000029FR-001, TM-638000029IT-001, TM-638000029JP-001, TM-638000029KR-001, TM-638000029MY-001, TM-638000029PL-001, TM-638000029RU-001, TM-638000029SK-001, TM-638000029SP-001, TM-638000029TH-001, TM-638000029TW-001, TM-638000029VN-001, TM-638004900-001, TM-638004900CN-001, TM-638004900SP-001



Series image - Reference only

EU ELV	
Not Relevant	
EU RoHS	
Not Reviewed	
REACH SVHC	
Not Reviewed	
Halogen-Free Status	
Not Relevant	
For more information, please visit Contact US	
China ROHS	Not Relevant
ELV	Not Relevant
RoHS Phthalates	Not Reviewed

Search Parts in this Series

207127 Series

Use With

Molex TM-3000: [638017200](#) , [638017300](#) , Molex TM-4000: [638017600](#) , Molex TM-2000: [638008300](#) , [638008400](#) , and Most Industry Standard Presses or Wire Process Machines

Application Tooling Description	FAQ Product #
2.54mm Pitch MX64 Terminal, Gold (Au) Plating, 0.35mm2 Wire, Left ReelPayoff, Also used with MX123 Female Receptacle Housing	334670021
2.54mm Pitch MX64 Terminal, Tin (Sn) Plating, 0.35mm2 Wire, Left Reel Payoff, Also used with MX123 Female Receptacle Housing	334680021

2.54mm Pitch MX64 [347360025](#)
Terminal, Silver
Plating, 0.35mm²,
Left Reel Payoff,
Also used with
MX123 Female
Receptacle Housing

This document was generated on 10/06/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

63902-5100