

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0639036700

Status:

Active

Overview:

Application Tooling

Description:

FineAdjust Applicator for Mini-Fit TPA2 Crimp Terminals, 16 AWG wires

Documents:

RoHS Certificate of Compliance (PDF)

General	
Product Family	Application Tooling
Series	207127
Comments	See Tooling Specification (PDF) Above
Function	Crimp
Geographic Area	Global
Level of Automation	Automatic, Semi-Automatic
More Detailed Tech Information	applicationtooling@molex.com
Overview	Application Tooling
Product Name	FineAdjust, Mini-Fit TPA2
Tool Type	Applicator
UPC	889056760140
Warranty Disclaimer	CAUTION: Molex tooling crimp specifications are valid only when used with Molex terminals and tooling manufactured by Molex and sold by Molex or authorized distributors ("Molex Tooling"). When using tooling other than Molex Tooling with Molex specific connector systems listed in our ATS documents, the Molex tooling qualification does not apply and the responsibility for full qualification of the connector system is that of the customer. Molex accepts no liability for connector performance or tooling support where tooling other than Molex Tooling is used or where Molex Tooling is modified.

Physical	
Net Weight	4980.585/g

Material Info

Reference - Drawing Numbers

Application Tooling Documents

ATS-639036700-001, TM-638000029-001, TM-638000029CN-001, TM-638000029DE-001, TM-638000029FR-001, TM-638000029IT-001, TM-638000029JP-001, TM-638000029KR-001, TM-638000029MY-001, TM-638000029PL-001, TM-638000029RU-001, TM-638000029SK-001, TM-638000029SP-001, TM-638000029TH-001, TM-638000029TW-001, TM-638000029VN-001, TM-638004900-001, TM-638004900CN-001, TM-638004900DE-001, TM-638004900FR-001, TM-638004900IT-001, TM-638004900JP-001, TM-638004900KR-001, TM-638004900MY-001, TM-638004900PL-001, TM-638004900RU-001, TM-638004900SK-001, TM-638004900SP-001, TM-638004900TH-001, TM-638004900TW-001, TM-638004900VN-001



Series image - Reference only

EU ELV	
Not Reviewed	
EU RoHS	China RoHS
Not Reviewed	
REACH SVHC	
Not Reviewed	
Halogen-Free	
Status	
Not Reviewed	
For more information, please visit Contact US	
China ROHS	Not Reviewed
ELV	Not Reviewed
RoHS Phthalates	Not Reviewed

Search Parts in this Series

207127 Series

Use With

Molex TM-3000: 638017200 , 638017300 , Molex TM-4000: 638017600 , Molex TM-2000: 638008300 , 638008400 , and Most Industry Standard Presses or Wire Process Machines

Application Tooling Description	FAQ Product #
Mini-Fit TPA2/ Sigma Female Crimp Terminal, Phosphor Bronze, Pre-Plated Tin (Sn), 16 AWG, 1.98-2.55mm Insulation Diameter, Reel	1727181111
Mini-Fit TPA2/ Sigma Female Crimp Terminal, Brass, Pre-Plated Tin (Sn), 16 AWG, 1.98-2.55mm Insulation Diameter, Reel	1727181121

Mini-Fit TPA2/ Sigma Male Crimp Terminal, Brass, Pre- Plated Tin (Sn), 16 AWG, 1.98-2.55mm Insulation Diameter, Reel	<u>1727651121</u>
Mini-Fit TPA2/ Sigma Female Crimp Terminal, Copper Alloy, Post- Plated Gold (Au), 16 AWG, 1.98-2.55mm Insulation Diameter, Reel	<u>2029881141</u>
Mini-Fit TPA2/ Sigma Female Crimp Terminal, Copper Alloy, Post- Plated Tin (Sn), 16 AWG, 1.98-2.55mm Insulation Diameter, Reel	<u>2029881241</u>
Mini-Fit TPA2/ Sigma Male Crimp Terminal, Copper Alloy, Post-Plated Gold (Au), 16 AWG, 1.98-2.55mm Insulation Diameter, Reel	<u>2030701141</u>
Mini-Fit TPA2/ Sigma Male Crimp Terminal, Copper Alloy, Post-Plated Tin (Sn), 16 AWG, 1.98-2.55mm Insulation Diameter, Reel	<u>2030701241</u>

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[63903-6700](#)