

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0639036800](#)
Status: **Active**
Overview: [Application Tooling](#)
Description: FineAdjust Applicator for Mini-Fit TPA2 Crimp Terminals, 0.50mm², 0.75mm² and 18-20 AWG wires

Documents:
[RoHS Certificate of Compliance \(PDF\)](#)

General	
Product Family	Application Tooling
Series	207127
Comments	See Tooling Specification (PDF) Above
Function	Crimp
Geographic Area	Global
Level of Automation	Automatic, Semi-Automatic
More Detailed Tech Information	applicationtooling@molex.com
Overview	Application Tooling
Product Name	FineAdjust, Mini-Fit TPA2
Tool Type	Applicator
UPC	889056436212
Warranty Disclaimer	CAUTION: Molex tooling crimp specifications are valid only when used with Molex terminals and tooling manufactured by Molex and sold by Molex or authorized distributors ("Molex Tooling"). When using tooling other than Molex Tooling with Molex specific connector systems listed in our ATS documents, the Molex tooling qualification does not apply and the responsibility for full qualification of the connector system is that of the customer. Molex accepts no liability for connector performance or tooling support where tooling other than Molex Tooling is used or where Molex Tooling is modified.

Material Info

Reference - Drawing Numbers
Application Tooling Documents

ATS-639036800-001, TM-638000029-001, TM-638000029CN-001, TM-638000029DE-001, TM-638000029FR-001, TM-638000029IT-001, TM-638000029JP-001, TM-638000029KR-001, TM-638000029MY-001, TM-638000029PL-001, TM-638000029RU-001, TM-638000029SK-001, TM-638000029SP-001, TM-638000029TH-001, TM-638000029TW-001, TM-638000029VN-001, TM-638004900-001, TM-638004900CN-001, TM-638004900DE-001, TM-638004900FR-001, TM-638004900IT-001, TM-638004900JP-001, TM-638004900KR-001, TM-638004900MY-001, TM-638004900PL-001, TM-638004900RU-001, TM-638004900SK-001, TM-638004900SP-001, TM-638004900TH-001, TM-638004900TW-001, TM-638004900VN-001



Series image - Reference only

EU ELV	
Not Relevant	
EU RoHS	
Not Relevant	
REACH SVHC	
Not Relevant	
Halogen-Free Status	
Not Relevant	
For more information, please visit Contact US	
China ROHS	Not Relevant
ELV	Not Relevant
RoHS Phthalates	Not Relevant

Search Parts in this Series
[207127](#) Series

Use With
Molex TM-3000: [638017200](#) , [638017300](#) , Molex TM-4000: [638017600](#) , Molex TM-2000: [638008300](#) , [638008400](#) , and Most Industry Standard Presses or Wire Process Machines

Application Tooling Description	FAQ Product #
Mini-Fit TPA2/ Sigma Female Crimp Terminal, Phosphor Bronze, Pre-Plated Tin (Sn), 18-20, 22+22 AWG, 2.10-2.85mm Insulation Diameter, Reel, Double Crimp Option	1727184111
Mini-Fit TPA2/ Sigma Female Crimp Terminal, Brass, Pre-Plated Tin (Sn), 18-20, 22+22	1727184121

AWG, 2.10-2.85mm Insulation Diameter, Reel, Double Crimp Option	
Mini-Fit TPA2/ Sigma Male Crimp Terminal, Brass, Pre-Plated Tin (Sn), 18-20, 22+22 AWG, 2.10-2.85mm Insulation Diameter, Reel, Double Crimp Option	<u>1727654121</u>
Mini-Fit TPA2/ Sigma Female Crimp Terminal, Copper Alloy, Post-Plated Gold (Au), 18-20, 22+22 AWG, 2.10-2.85mm Insulation Diameter, Reel	<u>2029884141</u>
Mini-Fit TPA2/ Sigma Female Crimp Terminal, Copper Alloy, Post-Plated Tin (Sn), 18-20, 22+22 AWG, 2.10-2.85mm Insulation Diameter, Reel	<u>2029884241</u>
Mini-Fit TPA2/ Sigma Male Crimp Terminal, Copper Alloy, Post-Plated Gold (Au), 18-20 AWG, 2.10-2.85mm Insulation Diameter, Reel	<u>2030704141</u>
Mini-Fit TPA2/ Sigma Male Crimp Terminal, Copper Alloy, Post-Plated Tin (Sn), 18-20 AWG, 2.10-2.85mm Insulation Diameter, Reel	<u>2030704241</u>

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[63903-6800](#)