

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0639037000](#)
Status: **Active**
Overview: [Application Tooling](#)
Description: FineAdjust Applicator for Mini-Fit TPA2 Crimp Terminals, 0.22mm², 0.25mm², 0.35 mm² and 22-24 AWG wires

Documents:
[RoHS Certificate of Compliance \(PDF\)](#)

General	
Product Family	Application Tooling
Series	207127
Comments	See Tooling Specification (PDF) Above
Function	Crimp
Geographic Area	Global
Level of Automation	Automatic, Semi-Automatic
More Detailed Tech Information	applicationtooling@molex.com
Overview	Application Tooling
Product Name	FineAdjust, Mini-Fit TPA2
Tool Type	Applicator
UPC	889056470575
Warranty Disclaimer	CAUTION: Molex tooling crimp specifications are valid only when used with Molex terminals and tooling manufactured by Molex and sold by Molex or authorized distributors ("Molex Tooling"). When using tooling other than Molex Tooling with Molex specific connector systems listed in our ATS documents, the Molex tooling qualification does not apply and the responsibility for full qualification of the connector system is that of the customer. Molex accepts no liability for connector performance or tooling support where tooling other than Molex Tooling is used or where Molex Tooling is modified.

Material Info

Reference - Drawing Numbers
[Application Tooling Documents](#)

ATS-639037000-001, TM-638000029-001, TM-638000029CN-001, TM-638000029DE-001, TM-638000029FR-001, TM-638000029IT-001, TM-638000029JP-001, TM-638000029KR-001, TM-638000029MY-001, TM-638000029PL-001, TM-638000029RU-001, TM-638000029SK-001, TM-638000029SP-001, TM-638000029TH-001, TM-638000029TW-001, TM-638000029VN-001, TM-638004900-001, TM-638004900CN-001, TM-638004900DE-001, TM-638004900FR-001, TM-638004900IT-001, TM-638004900JP-001, TM-638004900KR-001, TM-638004900MY-001, TM-638004900PL-001, TM-638004900RU-001, TM-638004900SK-001, TM-638004900SP-001, TM-638004900TH-001, TM-638004900TW-001, TM-638004900VN-001



Series image - Reference only

EU ELV Not Reviewed	
EU RoHS Not Reviewed	China RoHS
REACH SVHC Not Reviewed	
Halogen-Free Status Not Reviewed	
For more information, please visit Contact US	
China ROHS	Not Reviewed
ELV	Not Reviewed
RoHS Phthalates	Not Reviewed

Search Parts in this Series
[207127](#) Series

Use With
Molex TM-3000: [638017200](#) , [638017300](#) , Molex TM-4000: [638017600](#) , Molex TM-2000: [638008300](#) , [638008400](#) , and Most Industry Standard Presses or Wire Process Machines

Application Tooling Description	FAQ Product #
Mini-Fit TPA2/ Sigma Female Crimp Terminal, Phosphor Bronze, Pre-Plated Tin (Sn), 22-24 AWG, 1.65-2.38mm Insulation Diameter, Reel	1727186111
Mini-Fit TPA2/ Sigma Female Crimp Terminal, Brass, Pre-Plated Tin (Sn), 22-24 AWG, 1.65-2.38mm	1727186121

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[63903-7000](#)