

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0640010400

Status:

Active

Overview:

Application Tooling

Description:

PremiumGrade Hand Crimp Tool for Insulkrimp Quick Disconnect Terminals, 10-22 AWG



Documents:

RoHS Certificate of Compliance (PDF)

General	
Product Family	Application Tooling
Series	207129
Comments	Type RHT
Function	Crimp
Geographic Area	Global
Level of Automation	Manual
More Detailed Tech Information	applicationtooling@molex.com
Overview	Application Tooling
Product Name	N/A
Tool Type	Hand Crimp Tool
UPC	756054563687
Warranty Disclaimer	CAUTION: Molex tooling crimp specifications are valid only when used with Molex terminals and tooling manufactured by Molex and sold by Molex or authorized distributors ("Molex Tooling"). When using tooling other than Molex Tooling with Molex specific connector systems listed in our ATS documents, the Molex tooling qualification does not apply and the responsibility for full qualification of the connector system is that of the customer. Molex accepts no liability for connector performance or tooling support where tooling other than Molex Tooling is used or where Molex Tooling is modified.

Material Info	
Engineering Number	RHT-1994

Reference - Drawing Numbers	
Application Tooling Documents	ATS-640010400-001, TM-640160065-001, TM-640160065CN-001, TM-640160065DE-001, TM-640160065FR-001, TM-640160065IT-001, TM-640160065JP-001, TM-640160065KR-001, TM-640160065MY-001, TM-640160065PL-001, TM-640160065RU-001, TM-640160065SK-001, TM-640160065SP-001, TM-640160065TH-001, TM-640160065TW-001, TM-640160065VN-001

EU ELV	
Not Relevant	
EU RoHS	China RoHS
Not Reviewed	
REACH SVHC	
Not Contained Per - ED/61/2018 (27 June 2018)	
Halogen-Free	
Status	
Not Relevant	
For more information, please visit Contact US	
China ROHS	Not Relevant
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

207129 Series

Use With

Loose Piece Terminals

Application Tooling Description	FAQ Product #
InsulKrimp Quick Disconnect, Female, for 18-22 (0.80-0.35mm²), Bag, Tab 6.35 x 0.81mm, Salmon	190030001
InsulKrimp Quick Disconnect, Female, Box, Tab 6.35 x 0.81mm	190030005
InsulKrimp Quick Disconnect, Female, for 18-22 (0.80-0.35mm²), Box, Tab 6.35 x 0.81mm	190030008
InsulKrimp Quick Disconnect,	190030011

Female, for 18-22
(0.80-0.35mm²), Bag,
Tab 4.75 x 0.51mm,
Salmon
InsulKrimp Quick 190030014
Disconnect,
Female, for 18-22
(0.80-0.35mm²), Box,
Tab 4.75 x 0.51mm
InsulKrimp Quick 190030017
Disconnect,
Female, for 18-22
(0.80-0.35mm²), Bag,
Tab 4.75 x 0.81mm,
Pink
InsulKrimp Quick 190030021
Disconnect,
Female, for 18-22
(0.80-0.35mm²), Box,
Tab 4.75 x 0.81mm
InsulKrimp Quick 190030024
Disconnect,
Female, for 18-22
(0.80-0.35mm²), Bag,
Tab 2.79 x 0.51mm,
Salmon
InsulKrimp Quick 190030030
Disconnect,
Female, for 18-22
(0.80-0.35mm²), Bag,
Tab 2.79 x 0.81mm,
Pink
InsulKrimp Quick 190030036
Disconnect,
Female, for 18-22
(0.80-0.35mm²), Bag,
Tab 5.21 x 0.51mm,
Salmon
InsulKrimp Quick 190030038
Disconnect,
Female, for 18-22
(0.80-0.35mm²), Bag,
Tab 5.21 x 0.81mm,
Pink
InsulKrimp Quick 190030040
Disconnect,
Female, for 14-16
(2.00-1.30mm²), Bag,
Tab 6.35 x 0.81mm,
Blue
InsulKrimp Quick 190030044
Disconnect, Female,
Box, Tab 6.35 x
0.81mm
InsulKrimp Quick 190030047
Disconnect,
Female, for 14-16
(2.00-1.30mm²), Box,
Tab 6.35 x 0.81mm
InsulKrimp Quick 190030050
Disconnect,
Female, for 14-16
(2.00-1.30mm²), Bag,
Tab 4.75 x 0.51mm,
Blue

InsulKrimp Female Quick Disconnect, for 14-16 AWG Wire	<u>190030053</u>
InsulKrimp Quick Disconnect, Female, for 14-16 (2.00-1.30mm ²), Bag, Tab 4.75 x 0.81mm, Aqua	<u>190030056</u>
InsulKrimp Quick Disconnect, Female, for 14-16 (2.00-1.30mm ²), Box, Tab 4.75 x 0.81mm	<u>190030059</u>
InsulKrimp Quick Disconnect, Female, for 14-16 (2.00-1.30mm ²), Bag, Tab 5.21 x 0.51mm, Blue	<u>190030062</u>
InsulKrimp Quick Disconnect, Female, for 14-16 (2.00-1.30mm ²), Bag, Tab 5.21 x 0.81mm, Aqua	<u>190030063</u>
InsulKrimp Quick Disconnect, Female, Box, Tab 4.75 x 0.81mm	<u>190030129</u>
InsulKrimp Fully Insulated Female Quick Disconnect, for 10-12 AWG Wire, Box	<u>190050010</u>
Perma-Seal Female Quick Disconnect for 18-22 AWG Wire, Tab Size 6.35 x 0.81mm	<u>191640012</u>
Perma-Seal Female Quick Disconnect for 14-16 AWG Wire, Tab Size 6.35 x 0.81mm	<u>191640047</u>
Quixon Quick Disconnect, InsulKrimp Style, Female, Fully Insulated Red, 18-22 AWG, Loose	<u>192760002</u>
Quixon Quick Disconnect, InsulKrimp Style, Female, Fully Insulated Blue, 14-16 AWG, Loose	<u>192760005</u>

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

64001-0400