

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0640017400

Status:

Active

Overview:

Application Tooling

Description:

PremiumGrade Hand Crimp Tool for Industrial Terminals, 10-22 AWG (see ATS)

Documents:

RoHS Certificate of Compliance (PDF)

General

Product Family

Series

Comments

Function

Geographic Area

Level of Automation

More Detailed Tech Information

Overview

Product Name

Tool Type

UPC

Warranty Disclaimer

Application Tooling

207129

ServiceGrade Hand Tool 640160041. Type: 4C

Crimp

Global

Manual

applicationtooling@molex.com

Application Tooling

PremiumGrade

Hand Crimp Tool

800756778624

CAUTION: Molex tooling crimp specifications are valid only when used with Molex terminals and tooling manufactured by Molex and sold by Molex or authorized distributors ("Molex Tooling"). When using tooling other than Molex Tooling with Molex specific connector systems listed in our ATS documents, the Molex tooling qualification does not apply and the responsibility for full qualification of the connector system is that of the customer. Molex accepts no liability for connector performance or tooling support where tooling other than Molex Tooling is used or where Molex Tooling is modified.

Physical

Net Weight

742.798/g

Material Info

Reference - Drawing Numbers

Application Tooling Documents

ATS-640017400-001, TM-640160065-001, TM-640160065CN-001, TM-640160065DE-001, TM-640160065FR-001, TM-640160065IT-001, TM-640160065JP-001, TM-640160065KR-001, TM-640160065MY-001, TM-640160065PL-001, TM-640160065RU-001, TM-640160065SK-001, TM-640160065SP-001, TM-640160065TH-001, TM-640160065TW-001, TM-640160065VN-001



Series image - Reference only

EU ELV	
Not Relevant	
EU RoHS	China RoHS
Compliant	
REACH SVHC	
Not Reviewed	
Halogen-Free	
Status	
Not Relevant	
For more information, please visit Contact US	
China ROHS	Not Relevant
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

207129 Series

Use With

Loose Piece Terminals

Application Tooling Description	FAQ Product #
Perma-Seal Ring Tongue Terminal for 18-22 AWG Wire, Stud Size 10 (M5)	191640003
Perma-Seal Ring Tongue Terminal for 18-22 AWG Wire, Stud Size 1/4" (M6)	191640004
Perma-Seal Ring Tongue Terminal for 18-22 AWG Wire, Stud Size 3/8" (M9)	191640005
Perma-Seal Spade Tongue Terminal for 18-22 AWG Wire, Stud Size 6 (M3.5), Bag	191640006
Perma-Seal Spade Tongue Terminal for	191640007

18-22 AWG Wire,
Stud Size 8 (M4),
Bag
Perma-Seal Spade [191640008](#)
Tongue Terminal for
18-22 AWG Wire,
Stud Size 10 (M5),
Bag
Perma-Seal 3-Way [191640011](#)
Connector Assembly
for 18-22 AWG Wire
Perma-Seal Butt [191640013](#)
Splice for 18-22
AWG Wire
Perma-Seal Butt [191640014](#)
Splice for 18-22
AWG Wire, Mylar
Tape Carrier
Perma-Seal Ring [191640020](#)
Tongue Terminal for
14-16 AWG Wire,
Stud Size 3/8" (M9)
Perma-Seal Hook [191640021](#)
Tongue Terminal for
14-16 AWG Wire,
Stud Size 10 (M5)
Perma-Seal Ring [191640026](#)
Tongue Terminal for
14-16 AWG Wire,
Stud Size 1/4" (M6)
Perma-Seal Ring [191640027](#)
Tongue Terminal for
14-16 AWG Wire,
Stud Size 5/16" (M8)
Perma-Seal Spade [191640028](#)
Tongue Terminal
for 14-16 AWG
Wire, Stud Size 6
(M3.5),Bag
Perma-Seal Spade [191640029](#)
Tongue Terminal for
14-16 AWG Wire,
Stud Size 8 (M4)
Perma-Seal Spade [191640030](#)
Tongue Terminal for
14-16 AWG Wire,
Stud Size 10 (M5)
Perma-Seal Ring [191640032](#)
Tongue Terminal for
14-16 AWG Wire,
Stud Size 6 (M3.5)
Perma-Seal Ring [191640033](#)
Tongue Terminal for
14-16 AWG Wire,
Stud Size 8 (M4)
Perma-Seal Ring [191640034](#)
Tongue Terminal for
14-16 AWG Wire,
Stud Size 10 (M5)
Perma-Seal 3-Way [191640042](#)
Connector Assembly
for 14-16 AWG Wire
Perma-Seal Step [191640043](#)
Down Butt Splice for

14-16 AWG to 18-22

AWG Wire

Perma-Seal Butt 191640044

Splice for 14-16

AWG Wire

Perma-Seal Butt 191640045

Splice for 14-16

AWG Wire, Mylar

Tape Carrier

Perma-Seal Butt 191640056

Splice for 10-12

AWG Wire

Perma-Seal Butt 191640057

Splice for 10-12

AWG Wire, Mylar

Tape Carrier

Perma-Seal Ring 191640058

Tongue Terminal for

10-12 AWG Wire,

Stud Size 1/2" (M12)

Perma-Seal Ring 191640061

Tongue Terminal for

10-12 AWG Wire,

Stud Size 6 (M3.5)

Perma-Seal Ring 191640062

Tongue Terminal for

10-12 AWG Wire,

Stud Size 8 (M4)

Perma-Seal Ring 191640065

Tongue Terminal for

10-12 AWG Wire,

Stud Size 10 (M5)

Perma-Seal Ring 191640066

Tongue Terminal for

10-12 AWG Wire,

Stud Size 1/4" (M6)

Perma-Seal Ring 191640067

Tongue Terminal for

10-12 AWG Wire,

Stud Size 5/16" (M8)

Perma-Seal Ring 191640068

Tongue Terminal for

10-12 AWG Wire,

Stud Size 3/8" (M9)

Perma-Seal Spade 191640069

Tongue Terminal for

10-12 AWG Wire,

Stud Size 6 (M3.5)

Perma-Seal Spade 191640070

Tongue Terminal for

10-12 AWG Wire,

Stud Size 8 (M4)

Perma-Seal 3-Way 191640074

Connector Assembly

for 10-12 AWG Wire

Perma-Seal Step 191640077

Down Butt Splice

from 10-12 AWG to

14-16 AWG, Bag

Perma-Seal Ring 191640085

Tongue Terminal for

18-22 AWG Wire,

Stud Size 6 (M3.5),

Bag

Perma-Seal Ring	<u>191640086</u>
Tongue Terminal for	
18-22 AWG Wire,	
Stud Size 8 (M4)	
Perma-Seal Hook	<u>191640141</u>
Tongue Terminal for	
14-16 AWG Wire,	
Stud Size 6 (M3.5)	
Perma-Seal Hook	<u>191640142</u>
Tongue Terminal for	
14-16 AWG Wire,	
Stud Size 8 (M4)	
Perma-Seal Ring	<u>191640306</u>
Tongue Terminal for	
18-22 AWG Wire,	
Stud Size 10 (M5),	
Mylar Tape Carrier	
Perma-Seal Ring	<u>191640307</u>
Tongue Terminal for	
14-16 AWG Wire,	
Stud Size 3/8" (M9),	
Mylar Tape Carrier	
Perma-Seal Ring	<u>191640308</u>
Tongue Terminal for	
14-16 AWG Wire,	
Stud Size 1/4" (M6),	
Mylar Tape Carrier	
Perma-Seal Ring	<u>191640309</u>
Tongue Terminal for	
14-16 AWG Wire,	
Stud Size 5/16" (M8),	
Mylar Tape Carrier	
Perma-Seal Ring	<u>191640310</u>
Tongue Terminal for	
14-16 AWG Wire,	
Stud Size 6 (M3.5),	
Mylar Tape Carrier	
Perma-Seal Ring	<u>191640311</u>
Tongue Terminal for	
14-16 AWG Wire,	
Stud Size 8 (M4),	
Mylar Tape Carrier	
Perma-Seal Ring	<u>191640312</u>
Tongue Terminal for	
14-16 AWG Wire,	
Stud Size 10 (M5),	
Mylar Tape Carrier	
Perma-Seal Ring	<u>191640316</u>
Tongue Terminal for	
10-12 AWG Wire,	
Stud Size 10 (M5),	
Mylar Tape Carrier	
Perma-Seal Ring	<u>191640317</u>
Tongue Terminal for	
10-12 AWG Wire,	
Stud Size 1/4" (M6),	
Mylar Tape Carrier	
Perma-Seal Ring	<u>191640318</u>
Tongue Terminal for	
10-12 AWG Wire,	
Stud Size 5/16" (M8),	
Mylar Tape Carrier	
Perma-Seal Ring	<u>191640419</u>
Tongue Terminal for	
18-22 AWG Wire,	

Stud Size 8 (M4),
Mylar Tape Carrier
Perma-Seal Step 191640582
Down Butt Splice
from 10-12 AWG to
14-16 AWG, Tape
and Reel
Perma-Seal Spade 191640948
Tongue Terminal
for 14-16 AWG
Wire, Stud Size 6
(M3.5),Tape on Reel

This document was generated on 07/29/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[64001-7400](#)