

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0640030100](#)
Status: **Active**
Overview: [Application Tooling](#)
Description: PremiumGrade Hand Crimp Tool for Krimptite/Versakrimp Terminals and Splices, 10-22 AWG and 6.0mm² - 0.5mm²

Documents:
[RoHS Certificate of Compliance \(PDF\)](#)

General
Product Family Application Tooling
Series [207129](#)
Comments ServiceGrade Hand Tool [640160038](#) Type RHT
Function Crimp
Geographic Area Global
Level of Automation Manual
More Detailed Tech Information [applicationtooling@molex.com](#)
Overview [Application Tooling](#)
Product Name N/A
Tool Type Hand Crimp Tool
UPC 756054575499
Warranty Disclaimer CAUTION: Molex tooling crimp specifications are valid only when used with Molex terminals and tooling manufactured by Molex and sold by Molex or authorized distributors ("Molex Tooling"). When using tooling other than Molex Tooling with Molex specific connector systems listed in our ATS documents, the Molex tooling qualification does not apply and the responsibility for full qualification of the connector system is that of the customer. Molex accepts no liability for connector performance or tooling support where tooling other than Molex Tooling is used or where Molex Tooling is modified.

Physical
Net Weight 580.000/g

Material Info
Engineering Number RHT-1992

Reference - Drawing Numbers
Application Tooling Documents
ATS-640030100-001, TM-640160065-001, TM-640160065CN-001, TM-640160065DE-001, TM-640160065FR-001, TM-640160065IT-001, TM-640160065JP-001, TM-640160065KR-001, TM-640160065MY-001, TM-640160065PL-001, TM-640160065RU-001, TM-640160065SK-001, TM-640160065SP-001, TM-640160065TH-001, TM-640160065TW-001, TM-640160065VN-001



Series image - Reference only

EU ELV
Not Reviewed

EU RoHS	China RoHS
Not Reviewed	
REACH SVHC	
Not Contained Per - ED/61/2018 (27 June 2018)	
Halogen-Free Status	
Not Relevant	

For more information, please visit [Contact US](#)

China ROHS	Not Relevant
ELV	Not Reviewed
RoHS Phthalates	Not Contained

Search Parts in this Series
[207129](#) Series

Use With
Loose Piece Terminals

Application Tooling Description	FAQ Product #
Krimptite Quick Disconnect, Male, for 18-22 (0.80-0.35mm ²) Wire, Box, Tab 6.35 x 0.81mm	190220004
Krimptite Quick Disconnect, Male, for 14-16 AWG Wire, Box	190220018
Krimptite Snap Plug, for 18-22 AWG Wire	190330001
Krimptite Snap Plug, for 18-22 AWG Wire	190330003
Krimptite Ring Tongue Terminal for	190440168

14-16 Heavy Duty AWG Wire Krimptite Ring	<u>190440184</u>
Tongue Terminal for 14-16 Heavy Duty AWG Wire Krimptite Ring	<u>190440186</u>
Tongue Terminal for 14-16 Heavy Duty AWG Wire RING VERSAKRIMP	<u>190560083</u>
H/D (B-328-10HD) SPM Krimptite Ring	<u>190690027</u>
Tongue Terminal for 18-22 AWG Wire Krimptite Ring	<u>190690029</u>
Tongue Terminal for 18-22 AWG Wire Krimptite Ring	<u>190690031</u>
Tongue Terminal for 18-22 AWG Wire Krimptite Ring	<u>190690033</u>
Tongue Terminal for 18-22 AWG Wire Krimptite Ring	<u>190690035</u>
Tongue Terminal for 18-22 AWG Wire Krimptite Ring	<u>190690037</u>
Tongue Terminal for 18-22 AWG Wire Krimptite Ring	<u>190690040</u>
Tongue Terminal for 18-22 AWG Wire Krimptite Ring	<u>190690042</u>
Tongue Terminal for 18-22 AWG Wire Krimptite Ring	<u>190690045</u>
Tongue Terminal for 18-22 AWG Wire Krimptite Ring	<u>190690049</u>
Tongue Terminal for 18-22 AWG Wire Krimptite Ring	<u>190690052</u>
Tongue Terminal for 18-22 AWG Wire Krimptite Ring	<u>190690054</u>
Tongue Terminal for 18-22 AWG Wire Krimptite Ring	<u>190690056</u>
Tongue Terminal for 18-22 AWG Wire Krimptite Ring	<u>190690061</u>
Tongue Terminal for 18-22 AWG Wire Krimptite Ring	<u>190690093</u>
Tongue Terminal for 14-16 AWG Wire Krimptite Ring	<u>190690096</u>
Tongue Terminal for 14-16 AWG Wire Krimptite Ring	<u>190690099</u>
Tongue Terminal for 14-16 AWG Wire	

Krimptite Ring	<u>190690101</u>
Tongue Terminal for	
14-16 AWG Wire	
Krimptite Ring	<u>190690103</u>
Tongue Terminal for	
14-16 AWG Wire	
Krimptite Ring	<u>190690105</u>
Tongue Terminal for	
14-16 AWG Wire	
Krimptite Ring	<u>190690107</u>
Tongue Terminal for	
14-16 AWG Wire	
Krimptite Ring	<u>190690109</u>
Tongue Terminal for	
14-16 AWG Wire	
Krimptite Ring	<u>190690112</u>
Tongue Terminal for	
14-16 AWG Wire	
Krimptite Ring	<u>190690114</u>
Tongue Terminal for	
14-16 AWG Wire	
Krimptite Ring	<u>190690116</u>
Tongue Terminal for	
14-16 AWG Wire	
Krimptite Ring	<u>190690121</u>
Tongue Terminal for	
14-16 AWG Wire	
Krimptite Ring	<u>190690123</u>
Tongue Terminal for	
14-16 AWG Wire	
Krimptite Ring	<u>190690192</u>
Tongue Terminal for	
10-12 AWG Wire,	
Stud Size 1/2" (M12),	
Length 32.51mm	
Krimptite Ring	<u>190690196</u>
Tongue Terminal for	
10-12 AWG Wire,	
Stud Size 3/8" (M9),	
Length 32.51mm	
Krimptite Ring	<u>190690198</u>
Tongue Terminal	
for 10-12 AWG	
Wire, Stud Size	
7/16" (M11), Length	
32.51mm	
Krimptite Ring	<u>190690200</u>
Tongue Terminal for	
10-12 AWG Wire,	
Stud Size 4 (M2.6),	
Length 19.94mm	
Krimptite Ring	<u>190690202</u>
Tongue Terminal for	
10-12 AWG Wire,	
Stud Size 6 (M3.5),	
Length 19.94mm	
Krimptite Ring	<u>190690205</u>
Tongue Terminal for	
10-12 AWG Wire,	
Stud Size 8 (M4),	
Length 19.94mm	
Krimptite Ring	<u>190690209</u>
Tongue Terminal for	
10-12 AWG Wire,	

Stud Size 10 (M5), Length 19.94mm Krimptite Ring	<u>190690217</u>
Tongue Terminal for 10-12 AWG Wire, Stud Size 10 (M5), Length 24.18mm Krimptite Ring	<u>190690219</u>
Tongue Terminal for 10-12 AWG Wire, Stud Size 1/4" (M6), Length 24.18mm Krimptite Ring	<u>190690223</u>
Tongue Terminal for 10-12 AWG Wire, Stud Size 5/16" (M8), Length 24.18mm Krimptite Ring	<u>190690230</u>
Tongue Terminal for 10-12 AWG Wire, Stud Size 6 (M3.5), Length 18.82mm Krimptite Ring	<u>190690233</u>
Tongue Terminal for 10-12 AWG Wire, Stud Size 8 (M4), Length 18.82mm Krimptite Ring	<u>190690236</u>
Tongue Terminal for 10-12 AWG Wire Krimptite Ring	<u>190690238</u>
Tongue Terminal for 10-12 AWG Wire, Stud Size 1/4" (M6), Length 26.82mm Krimptite Ring	<u>190690241</u>
Tongue Terminal for 10-12 AWG Wire, Stud Size 3/8" (M9), Length 26.82mm Krimptite Ring	<u>190690244</u>
Tongue Terminal for 10-12 AWG Wire, Stud Size 5/16" (M8), Length 26.82mm Krimptite Snap	<u>190980017</u>
Spade Terminal, for 18-22 AWG Wire, Stud Size 5 (M3), 14.86mm Length Krimptite Snap	<u>190980018</u>
Spade Terminal, for 18-22 AWG Wire, Stud Size 5-6 (M3-3.5), 14.86mm Length Krimptite Snap	<u>190980023</u>
Spade Terminal, for 18-22 AWG Wire, Stud Size 8 (M4), 16.41mm Length Krimptite Snap	<u>190980024</u>
Spade Terminal, for 18-22 AWG Wire,	

	Stud Size 10 (M5), 17.60mm Length Krimptite Snap <u>190980041</u> Spade Terminal, for 14-16 AWG Wire, Stud Size 5 (M3), 14.86mm Length Krimptite Snap <u>190980043</u> Spade Terminal, for 14-16 AWG Wire, Stud Size 5-6 (M3-3.5), 14.86mm Length Krimptite Snap <u>190980047</u> Spade Terminal, for 14-16 AWG Wire, Stud Size 8 (M4), 16.41mm Length Krimptite Snap <u>190980049</u> Spade Terminal, for 14-16 AWG Wire, Stud Size 10 (M5), 17.60mm Length Krimptite Snap <u>190980069</u> Spade Terminal, for 10-12 AWG Wire, Stud Size 5-6 (M3-3.5), 16.87mm Length Krimptite Snap <u>190980074</u> Spade Terminal, for 10-12 AWG Wire, Stud Size 10 (M5), 19.60mm Length Krimptite Flanged <u>191180021</u> Spade Tongue Terminal for 18-22 AWG Wire, Stud Size 6 (M3.5), Length 14.12mm Krimptite Flanged <u>191180025</u> Spade Tongue Terminal for 18-22 AWG Wire, Stud Size 10 (M5) Krimptite Flanged <u>191180080</u> Spade Tongue Terminal for 10-12 AWG Wire, Stud Size 8 (M4), Length 19.91mm Krimptite Flanged <u>191180082</u> Spade Tongue Terminal for 10-12 AWG Wire, Stud Size 10 (M5), Length 19.91mm Krimptite Flanged <u>191180086</u> Spade Tongue Terminal for 10-12 AWG Wire, Stud Size 8 (M4), Length 19.56mm Krimptite Flanged <u>191180088</u> Spade Tongue
--	---

Terminal for 10-12 AWG Wire, Stud Size 10 (M5), Length 19.56mm Krimptite Block	<u>191290005</u>
Spade Terminal for 10-12 AWG Wire Krimptite Block	<u>191290007</u>
Spade Terminal for 10-12 AWG Wire Krimptite Block	<u>191290008</u>
Spade Terminal for 10-12 AWG Wire Krimptite Block	<u>191290039</u>
Spade Terminal for 18-22 AWG Wire Krimptite Block	<u>191290041</u>
Spade Terminal for 18-22 AWG Wire Krimptite Block	<u>191290043</u>
Spade Terminal for 18-22 AWG Wire Krimptite Block	<u>191290045</u>
Spade Terminal for 18-22 AWG Wire Krimptite Block	<u>191290047</u>
Spade Terminal for 18-22 AWG Wire Krimptite Block	<u>191290053</u>
Spade Terminal for 18-22 AWG Wire Krimptite Block	<u>191290055</u>
Spade Terminal for 18-22 AWG Wire Krimptite Spade	<u>191400035</u>
Tongue Terminal for 18-22 AWG Wire,Non-Insulated, Stud Size 6 Krimptite Spade	<u>191400090</u>
Tongue Terminal for 14-16 AWG Wire, Non-Insulated, Stud Size 6 Krimptite Spade	<u>191410020</u>
Tongue Terminal for 18-22 AWG Wire, Stud Size 6 (M3.5) Krimptite Spade	<u>191410022</u>
Tongue Terminal for 18-22 AWG Wire, Stud Size 8 (M4) Krimptite Spade	<u>191410024</u>
Tongue Terminal for 18-22 AWG Wire, Stud Size 10 (M5) Krimptite Spade	<u>191410056</u>
Tongue Terminal for 14-16 AWG Wire Krimptite Spade	<u>191410058</u>
Tongue Terminal for 14-16 AWG Wire Krimptite Spade	<u>191410063</u>
Tongue Terminal for 14-16 AWG Wire	

Krimptite Spade Tongue Terminal for 14-16 AWG Wire	<u>191410065</u>
Krimptite Spade Tongue Terminal for 10-12 AWG Wire	<u>191410081</u>
Krimptite Spade Tongue Terminal for 10-12 AWG Wire	<u>191410083</u>
Krimptite Spade Tongue Terminal for 10-12 AWG Wire	<u>191410085</u>
VersaKrimp Block Spade Terminal for 18-22 AWG Wire	<u>191470019</u>
VersaKrimp Block Spade Terminal for 14-16 AWG Wire	<u>191470057</u>
VersaKrimp Block Spade Terminal for 14-16 AWG Wire	<u>191470062</u>
VersaKrimp Block Spade Terminal for 10-12 AWG Wire	<u>191470090</u>
VersaKrimp Spade Tongue Terminal for 10-12 AWG Wire	<u>191470096</u>
Krimptite Butt Splice for 10-12 AWG Wire	<u>191890015</u>
VersaKrimp Ring Tongue Terminal for 18-22 AWG Wire	<u>191930007</u>
VersaKrimp Ring Tongue Terminal for 18-22 AWG Wire	<u>191930009</u>
VersaKrimp Ring Tongue Terminal for 18-22 AWG Wire	<u>191930014</u>
VersaKrimp Ring Tongue Terminal for 18-22 AWG Wire	<u>191930016</u>
VersaKrimp Ring Tongue Terminal for 18-22 AWG Wire	<u>191930023</u>
VersaKrimp Ring Tongue Terminal for 18-22 AWG Wire	<u>191930041</u>
VersaKrimp Ring Tongue Terminal for 16-14 AWG Wire, Stud Size 1/4" (M6)	<u>191930055</u>
VersaKrimp Ring Tongue Terminal for 14-16 AWG Wire	<u>191930057</u>
VersaKrimp Ring Tongue Terminal for 14-16 AWG Wire	<u>191930062</u>
VersaKrimp Ring Tongue Terminal for 14-16 AWG Wire	<u>191930072</u>
VersaKrimp Ring Tongue Terminal for 14-16 AWG Wire	<u>191930074</u>

VersaKrimp Ring Tongue Terminal for 14-16 AWG Wire	<u>191930078</u>
VersaKrimp Ring Tongue Terminal for 14-16 AWG Wire	<u>191930080</u>
VersaKrimp Ring Tongue Terminal for 14-16 AWG Wire	<u>191930082</u>
VersaKrimp Ring Tongue Terminal for 14-16 AWG Wire	<u>191930089</u>
VersaKrimp Ring Tongue Terminal for 14-16 AWG Wire	<u>191930091</u>
VersaKrimp Ring Tongue Terminal for 10-12 AWG Wire	<u>191930094</u>
VersaKrimp Ring Tongue Terminal for 10-12 AWG Wire	<u>191930097</u>
VersaKrimp Ring Tongue Terminal for 10-12 AWG Wire	<u>191930099</u>
VersaKrimp Ring Tongue Terminal for 10-12 AWG Wire	<u>191930103</u>
VersaKrimp Ring Tongue Terminal for 10-12 AWG Wire	<u>191930106</u>
VersaKrimp Ring Tongue Terminal for 10-12 AWG Wire,	<u>191930109</u>
Loose METRIC RING VERSAKRIMP C-328-209 SPM	<u>191930112</u>
VersaKrimp Ring Tongue Terminal for 10-12 AWG Wire	<u>191930116</u>
VersaKrimp Ring Tongue Terminal for 10-12 AWG Wire	<u>191930120</u>
VersaKrimp Ring Tongue Terminal for 10-12 AWG Wire	<u>191930128</u>
VersaKrimp Ring Tongue Terminal for 10-12 AWG Wire	<u>191930130</u>
VersaKrimp Ring Tongue Terminal for 10-12 AWG Wire	<u>191930134</u>
VersaKrimp Ring Tongue Terminal for 10-12 AWG Wire,	<u>191930137</u>
3/8" (M9) Stud Size VersaKrimp Ring Tongue Terminal for 10-12 AWG Wire	<u>191930141</u>
RING VERSAKRIMP BENT (C-328-10R90)	<u>191930532</u>
VersaKrimp Temp- Term Ring Tongue Terminal for 14 to	<u>192030063</u>

16 AWG Wire, Stud Size 10 (M5)	
Krimptite Temp-Term Ring Tongue Terminal for 14 to 16 AWG Wire, Stud Size 8 (M4)	<u>192030083</u>
Krimptite Temp-Term Ring Tongue Terminal for 14 to 16 AWG Wire, Stud Size 10 (M5)	<u>192030085</u>
VersaKrimp Temp-Term Ring Tongue Terminal for 10 to 12 AWG Wire, Stud Size 10 (M5)	<u>192030099</u>
Krimptite Temp-Term Ring Tongue Terminal for 10 to 12 AWG Wire, Stud Size 10 (M5)	<u>192030113</u>
VersaKrimp Temp-Term Ring Tongue Terminal for 14 to 16 AWG Wire, Stud Size 1/4" (M6)	<u>192030148</u>
VersaKrimp Temp-Term Ring Tongue Terminal for 10 to 12 AWG Wire, Stud Size 8 (M4)	<u>192030156</u>
VersaKrimp Temp-Term Ring Tongue Terminal for 10 to 12 AWG Wire, Stud Size 3/8" (M9)	<u>192030158</u>
HI-TEMP PARALLEL SPLICE (C-T-303)	<u>192030169</u>
VersaKrimp Temp-Term Ring Tongue Terminal for 10 to 12 AWG Wire, Stud Size 1/4" (M6)	<u>192030182</u>
Krimptite Temp-Term Butt Splice for 12-10 AWG Wire, 483°C (900° F), Loose Piece	<u>192030386</u>
VersaKrimp Parallel Splice for 14-16 AWG Wire	<u>192050001</u>
VersaKrimp Parallel Splice for 10-12 AWG Wire	<u>192050003</u>
VersaKrimp Parallel Splice for 18-22 AWG Wire	<u>192070001</u>
Krimptite Wire Pin Terminal for 12-10 AWG Wire	<u>192110001</u>
Krimptite Wire Pin Terminal for 22-18 AWG Wire	<u>192110003</u>

	Krimptite Wire Pin Terminal for 16-14 AWG Wire	<u>192110005</u>
	VersaKrimp Butt Splice for 18-22 AWG Wire	<u>192150009</u>
	Step Down Butt Splice for 14-22 AWG Wire	<u>192150013</u>
	VersaKrimp Butt Splice for 14-16 AWG Wire	<u>192150018</u>
	Step Down Butt Splice for 10-16 AWG Wire	<u>192150023</u>
	VersaKrimp Butt Splice for 10-12 AWG Wire	<u>192150028</u>
	VersaKrimp Metric Ring Terminal for M2.5 Stud Size (#4), Un-insulated	<u>193230001</u>
	VersaKrimp Metric Ring Terminal for M3 Stud Size (#5), Un-insulated	<u>193230002</u>
	VersaKrimp Metric Ring Terminal for M3-3.5 Stud Size (#5-#6), Un-insulated	<u>193230003</u>
	VersaKrimp Metric Ring Terminal for M4 Stud Size (#8), Un-insulated	<u>193230004</u>
	VersaKrimp Metric Ring Terminal for M5 Stud Size (#10), Un-insulated	<u>193230005</u>
	VersaKrimp Metric Ring Terminal for M3 Stud Size (#5), Un-insulated	<u>193230006</u>
	VersaKrimp Metric Ring Terminal for M3-3.5 Stud Size (#5-#6), Un-insulated	<u>193230007</u>
	VersaKrimp Metric Ring Terminal for M4 Stud Size (#8), Un-insulated	<u>193230008</u>
	VersaKrimp Metric Ring Terminal for M5 Stud Size (#10), Un-insulated	<u>193230009</u>
	VersaKrimp Metric Ring Terminal for M6 Stud Size (1/4"), Un-insulated	<u>193230010</u>
	VersaKrimp Metric Ring Terminal for M8 Stud Size (5/16"), Un-insulated	<u>193230011</u>
	VersaKrimp Metric Ring Terminal for M4	<u>193230012</u>

Stud Size (#8), Un-insulated	
VersaKrimp Metric	<u>193230013</u>
Ring Terminal for M3	
Stud Size (#5), Un-insulated	
VersaKrimp Metric	<u>193230014</u>
Ring Terminal for M6	
Stud Size (1/4"), Un-insulated	
VersaKrimp Metric	<u>193230015</u>
Ring Terminal for M8	
Stud Size (5/16"), Un-insulated	
VersaKrimp Metric	<u>193230016</u>
Ring Terminal for M10	
Stud Size (7/16"), Un-insulated	

This document was generated on 07/30/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[64003-0100](#)