

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0640038370

Status:

Active

Overview:

Application Tooling

Description:

Square "Din" Style Die Set for BCL and VersaKrimp Un-insulated Ring Tongue
Terminals and Splices, 4/0 AWG



Documents:

RoHS Certificate of Compliance (PDF)

General	
Product Family	Application Tooling
Series	207126
Comments	See Tooling Specification (PDF) Above
Function	Crimp
Geographic Area	Global
Level of Automation	Manual
More Detailed Tech Information	applicationtooling@molex.com
Overview	Application Tooling
Product Name	Battery Cable Lug, VersaKrimp
Tool Type	Crimp Module
UPC	889056283236
Warranty Disclaimer	CAUTION: Molex tooling crimp specifications are valid only when used with Molex terminals and tooling manufactured by Molex and sold by Molex or authorized distributors ("Molex Tooling"). When using tooling other than Molex Tooling with Molex specific connector systems listed in our ATS documents, the Molex tooling qualification does not apply and the responsibility for full qualification of the connector system is that of the customer. Molex accepts no liability for connector performance or tooling support where tooling other than Molex Tooling is used or where Molex Tooling is modified.

Material Info

Reference - Drawing Numbers

Application Tooling Documents

ATS-638161100-001, ATS-640038370-001,
TM-638161000-001

EU ELV	
Not Reviewed	
EU RoHS	China RoHS
Not Reviewed	
REACH SVHC	
Not Reviewed	
Halogen-Free	
Status	
Not Reviewed	
For more information, please visit Contact US	
China ROHS	Not Reviewed
ELV	Not Reviewed
RoHS Phthalates	Not Reviewed

Search Parts in this Series

207126 Series

Application Tooling Description	FAQ Product #
VersaKrimp Ring Tongue Terminal for 4/0 AWG Wire	191930372
VersaKrimp Ring Tongue Terminal for 4/0 AWG Wire	191930375
VersaKrimp Butt Splice for 4/0 AWG Wire	192050013
VersaKrimp Parallel Splice for 4/0 AWG Wire	192150050
Compression Style Ring Tongue Terminal for 4/0 AWG Wire, Stud Size 3/8" (M9), Plated, Barrel Length 19.05mm	192210250
Compression Style Ring Tongue Terminal for 4/0	192210251

AWG Wire, Stud Size 1/2" (M12), Plated, Barrel Length 19.05mm Compression	<u>192210382</u>
Style Ring Tongue Terminal for 4/0 AWG Cable, Stud Size 3/8" (M9), Unplated, Barrel Length 19.05mm Compression	<u>192210403</u>
Style Ring Tongue Terminal for 4/0 AWG Wire, Stud Size 1/2" (M12), Unplated, Barrel Length 19.05mm Compression Ring	<u>192210412</u>
Tongue Terminal for 4/0 AWG Wire, Stud Size 5/16" (M8), Plated, Barrel Length 19.05mm Compression	<u>192210413</u>
Style Ring Tongue Terminal for 4/0 AWG Wire, Stud Size 5/16" (M8), Unplated, Barrel Length 19.05mm Compression	<u>192210648</u>
Style Ring Tongue Terminal for 4/0 AWG Wire, Stud Size 1/4" (M6), Plated, Barrel Length 19.05mm Compression	<u>192210652</u>
Style Ring Tongue Terminal for 4/0 AWG Wire, Stud Size 1/4" (M6), Unplated, Barrel Length 19.05mm	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

<u>63869-0270</u>	<u>11-18-3149</u>	<u>63903-7470</u>	<u>90-32-3130</u>	<u>64003-8370</u>	<u>63904-1470</u>	<u>63800-8499</u>	<u>90-32-3290</u>	<u>63903-7170</u>
<u>63903-8570</u>	<u>63801-3301</u>	<u>63903-9970</u>	<u>63800-7999</u>	<u>90-32-7010</u>	<u>63904-0270</u>	<u>63903-9870</u>	<u>69890-2300</u>	<u>63903-8470</u>
<u>63800-8396</u>	<u>62202-0199</u>							