

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0640050400

Status:

Active

Overview:

Application Tooling

Description:

Crimp Head for the AT-200 Pneumatic Hand Tool

Documents:

RoHS Certificate of Compliance (PDF)

General	
Product Family	Application Tooling
Series	207129
Comments	Type: AT
Function	Crimp
Geographic Area	Global
Level of Automation	Manual
More Detailed Tech Information	applicationtooling@molex.com
Overview	Application Tooling
Product Name	Air Tool
Tool Type	Pneumatic Hand Tool
UPC	756054563700
Warranty Disclaimer	CAUTION: Molex tooling crimp specifications are valid only when used with Molex terminals and tooling manufactured by Molex and sold by Molex or authorized distributors ("Molex Tooling"). When using tooling other than Molex Tooling with Molex specific connector systems listed in our ATS documents, the Molex tooling qualification does not apply and the responsibility for full qualification of the connector system is that of the customer. Molex accepts no liability for connector performance or tooling support where tooling other than Molex Tooling is used or where Molex Tooling is modified.

Material Info

Engineering Number

AT-1994

Reference - Drawing Numbers

Application Tooling Documents

ATS-640050400-001, TM-192790001-001, TM-192790001SP-001, TM-640160065-001, TM-640160065CN-001, TM-640160065DE-001, TM-640160065FR-001, TM-640160065IT-001, TM-640160065JP-001, TM-640160065KR-001, TM-640160065MY-001, TM-640160065PL-001, TM-640160065RU-001, TM-640160065SK-001, TM-640160065SP-001, TM-640160065TH-001, TM-640160065TW-001, TM-640160065VN-001



Series image - Reference only

EU ELV	
Not Relevant	
EU RoHS	China RoHS
Compliant	
REACH SVHC	
Not Contained Per - ED/30/2017 (7 July 2017)	
Halogen-Free	
Status	
Not Relevant	
For more information, please visit Contact US	
China ROHS	Not Relevant
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

207129 Series

Use With

Molex AT-200 HandHeld Pneumatic Tool

192790001

Application Tooling Description	FAQ Product #
InsulKrimp Quick Disconnect, Female, for 18-22 (0.80-0.35mm²), Bag, Tab 6.35 x 0.81mm, Salmon	190030001
InsulKrimp Quick Disconnect, Female, Box, Tab 6.35 x 0.81mm	190030005
InsulKrimp Quick Disconnect, Female, for 18-22 (0.80-0.35mm²), Box, Tab 6.35 x 0.81mm	190030008

InsulKrimp Quick Disconnect, Female, for 18-22 (0.80-0.35mm²), Bag, Tab 4.75 x 0.51mm, Salmon	<u>190030011</u>
InsulKrimp Quick Disconnect, Female, for 18-22 (0.80-0.35mm²), Box, Tab 4.75 x 0.51mm	<u>190030014</u>
InsulKrimp Quick Disconnect, Female, for 18-22 (0.80-0.35mm²), Bag, Tab 4.75 x 0.81mm, Pink	<u>190030017</u>
InsulKrimp Quick Disconnect, Female, for 18-22 (0.80-0.35mm²), Box, Tab 4.75 x 0.81mm	<u>190030021</u>
InsulKrimp Quick Disconnect, Female, for 18-22 (0.80-0.35mm²), Bag, Tab 2.79 x 0.51mm, Salmon	<u>190030024</u>
InsulKrimp Quick Disconnect, Female, for 18-22 (0.80-0.35mm²), Bag, Tab 2.79 x 0.81mm, Pink	<u>190030030</u>
InsulKrimp Quick Disconnect, Female, for 18-22 (0.80-0.35mm²), Bag, Tab 5.21 x 0.51mm, Salmon	<u>190030036</u>
InsulKrimp Quick Disconnect, Female, for 18-22 (0.80-0.35mm²), Bag, Tab 5.21 x 0.81mm, Pink	<u>190030038</u>
InsulKrimp Quick Disconnect, Female, for 14-16 (2.00-1.30mm²), Bag, Tab 6.35 x 0.81mm, Blue	<u>190030040</u>
InsulKrimp Quick Disconnect, Female, Box, Tab 6.35 x 0.81mm	<u>190030044</u>
InsulKrimp Quick Disconnect, Female, for 14-16 (2.00-1.30mm²), Box, Tab 6.35 x 0.81mm	<u>190030047</u>
InsulKrimp Quick Disconnect, Female, for 14-16 (2.00-1.30mm²), Bag,	<u>190030050</u>

Tab 4.75 x 0.51mm,
Blue
InsulKrimp Female [190030053](#)
Quick Disconnect, for
14-16 AWG Wire
InsulKrimp Quick [190030056](#)
Disconnect,
Female, for 14-16
(2.00-1.30mm²), Bag,
Tab 4.75 x 0.81mm,
Aqua
InsulKrimp Quick [190030059](#)
Disconnect,
Female, for 14-16
(2.00-1.30mm²), Box,
Tab 4.75 x 0.81mm
InsulKrimp Quick [190030062](#)
Disconnect,
Female, for 14-16
(2.00-1.30mm²), Bag,
Tab 5.21 x 0.51mm,
Blue
InsulKrimp Quick [190030063](#)
Disconnect,
Female, for 14-16
(2.00-1.30mm²), Bag,
Tab 5.21 x 0.81mm,
Aqua
InsulKrimp Quick [190030129](#)
Disconnect, Female,
Box, Tab 4.75 x
0.81mm
Perma-Seal Female [191640012](#)
Quick Disconnect for
18-22 AWG Wire,
Tab Size 6.35 x
0.81mm
Perma-Seal Female [191640047](#)
Quick Disconnect for
14-16 AWG Wire,
Tab Size 6.35 x
0.81mm
Quixon Quick [192760002](#)
Disconnect,
InsulKrimp Style,
Female, Fully
Insulated Red, 18-22
AWG, Loose
Quixon Quick [192760005](#)
Disconnect,
InsulKrimp Style,
Female, Fully
Insulated Blue, 14-16
AWG, Loose

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[64005-0400](#)