

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0640054700

Status:

Active

Overview:

Application Tooling

Description:

Crimp Head for the AT-200 Pneumatic Hand Tool

Documents:

RoHS Certificate of Compliance (PDF)

General	
Product Family	Application Tooling
Series	207129
Comments	Type: AT
Function	Crimp
Geographic Area	Global
Level of Automation	Manual
More Detailed Tech Information	applicationtooling@molex.com
Overview	Application Tooling
Product Name	Air Tool
Tool Type	Pneumatic Hand Tool
UPC	822348114108
Warranty Disclaimer	CAUTION: Molex tooling crimp specifications are valid only when used with Molex terminals and tooling manufactured by Molex and sold by Molex or authorized distributors ("Molex Tooling"). When using tooling other than Molex Tooling with Molex specific connector systems listed in our ATS documents, the Molex tooling qualification does not apply and the responsibility for full qualification of the connector system is that of the customer. Molex accepts no liability for connector performance or tooling support where tooling other than Molex Tooling is used or where Molex Tooling is modified.

Material Info

Engineering Number

AT-2761-CC

Reference - Drawing Numbers

Application Tooling Documents

ATS-640054700-001, TM-192790001-001, TM-192790001SP-001, TM-640160065-001, TM-640160065CN-001, TM-640160065DE-001, TM-640160065FR-001, TM-640160065IT-001, TM-640160065JP-001, TM-640160065KR-001, TM-640160065MY-001, TM-640160065PL-001, TM-640160065RU-001, TM-640160065SK-001, TM-640160065SP-001, TM-640160065TH-001, TM-640160065TW-001, TM-640160065VN-001



Series image - Reference only

EU ELV	
Not Relevant	
EU RoHS	China RoHS
Compliant	
REACH SVHC	
Not Contained Per - ED/30/2017 (7 July 2017)	
Halogen-Free	
Status	
Not Relevant	
For more information, please visit Contact US	
China ROHS	Not Relevant
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

207129 Series

Use With

Molex AT-200 HandHeld Pneumatic Tool

192790001

Application Tooling Description	FAQ Product #
InsulKrimp Fully Insulated Coupler, Male, for 18-22 AWG Wire, Box	190040001
InsulKrimp Fully Insulated Coupler, Male, for 14-16 AWG Wire, Box	190040005
InsulKrimp Fully Insulated Coupler, Female, for 18-22 AWG Wire, Box	190050001
InsulKrimp Fully Insulated Coupler, Female, for 14-16 AWG Wire, Box	190050005

Perma-Seal Male 191640015
Quick Disconnect
Tab for 18-22 AWG
Wire, Tab Size 6.35
x 0.81mm, Bag
Perma-Seal Female 191640017
Quick Disconnect
Receptacle for 18-22
AWG Wire, Tab Size
6.35 x 0.81mm
Perma-Seal Male 191640048
Quick Disconnect
Tab for 14-16 AWG
Wire, Tab Size 6.35
x 0.81mm, Bag
Perma-Seal Female 191640050
Quick Disconnect
Receptacle for 14-16
AWG Wire, Tab Size
6.35 x 0.81mm
Perma-Seal Snap 191640052
Receptacle for 18-22
AWG Wire, Diameter
3.96mm
Perma-Seal Snap 191640053
Receptacle for 18-22
AWG Wire, Diameter
4.57mm

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[64005-4700](#)