

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0640071100

Status:

Active

Overview:

Application Tooling

Description:

Crimp Head for the AT-200 Pneumatic Hand Tool

Documents:

RoHS Certificate of Compliance (PDF)

General	
Product Family	Application Tooling
Series	207129
Comments	Type: AT
Function	Crimp
Geographic Area	Global
Level of Automation	Manual
More Detailed Tech Information	applicationtooling@molex.com
Overview	Application Tooling
Product Name	Air Tool
Tool Type	Pneumatic Hand Tool
UPC	822348563845
Warranty Disclaimer	CAUTION: Molex tooling crimp specifications are valid only when used with Molex terminals and tooling manufactured by Molex and sold by Molex or authorized distributors ("Molex Tooling"). When using tooling other than Molex Tooling with Molex specific connector systems listed in our ATS documents, the Molex tooling qualification does not apply and the responsibility for full qualification of the connector system is that of the customer. Molex accepts no liability for connector performance or tooling support where tooling other than Molex Tooling is used or where Molex Tooling is modified.

Material Info

Engineering Number

AT-1751

Reference - Drawing Numbers

Application Tooling Documents

ATS-640071100-001, TM-192790001-001, TM-192790001SP-001, TM-640160065-001, TM-640160065CN-001, TM-640160065DE-001, TM-640160065FR-001, TM-640160065IT-001, TM-640160065JP-001, TM-640160065KR-001, TM-640160065MY-001, TM-640160065PL-001, TM-640160065RU-001, TM-640160065SK-001, TM-640160065SP-001, TM-640160065TH-001, TM-640160065TW-001, TM-640160065VN-001



Series image - Reference only

EU ELV	
Not Relevant	
EU RoHS	China RoHS
Compliant	
REACH SVHC	
Not Contained Per - ED/30/2017 (7 July 2017)	
Halogen-Free	
Status	
Not Relevant	
For more information, please visit Contact US	
China ROHS	Not Relevant
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

207129 Series

Use With

Molex AT-200 HandHeld Pneumatic Tool

192790001

Application Tooling Description	FAQ Product #
Krimptite Quick Disconnect, Female, for 18-22 (0.80-0.35mm ²) Wire, Box, Tab 2.79 x 0.51mm	190160001
Krimptite Quick Disconnect, Female, for 18-22 (0.80-0.35mm ²) Wire, Box, Tab 2.79 x 0.81mm	190160003
Krimptite Quick Disconnect, Female, for 18-22 (0.80-0.35mm ²) Wire,	190160005

Box, Tab 4.75 x
0.51mm
Krimptite Quick 190160009
Disconnect,
Female, for 18-22
(0.80-0.35mm²) Wire,
Box, Tab 6.35 x
0.81mm
Krimptite Quick 190160035
Disconnect,
Female, for 14-16
(2.00-1.30mm²) Wire,
Box, Tab 2.79 x
0.51mm
Krimptite Quick 190160037
Disconnect,
Female, for 14-16
(2.00-1.30mm²) Wire,
Box, Tab 2.79 x
0.81mm
Krimptite Quick 190160039
Disconnect,
Female, for 14-16
(2.00-1.30mm²) Wire,
Box, Tab 4.75 x
0.51mm
Krimptite Quick 190160040
Disconnect,
Female, for 14-16
(2.00-1.30mm²) Wire,
Box, Tab 4.75 x
0.81mm
Krimptite Quick 190160111
Disconnect,
Female, for 14-16
(2.00-1.30mm²) Wire,
Box, Tab 6.35 x
0.81mm
Krimptite Snap 190370002
Plug Receptacle,
for 18-22 AWG
Wire, Box, 16.26mm
Length
Krimptite Snap 190370004
Plug Receptacle,
for 14-16 AWG
Wire, Box, 16.26mm
Length
Krimptite Snap 190370006
Plug Receptacle,
for 14-16 AWG
Wire, Box, 17.80mm
Length
Krimptite Snap 190370015
Plug Receptacle,
for 18-22 AWG
Wire, Box, 17.80mm
Length
Krimptite Quick 192030390
Disconnect, Female,
Steel, 483°C (900°
F), 14-16 AWG, Tab
6.35mm
Quixon Quick 192730007
Disconnect, Krimptite

Style, Female, Un-
insulated, 18-20
AWG, Loose
Quixon Quick 192730008
Disconnect, Krimptite
Style, Female, Un-
insulated, 14-16
AWG, Loose

This document was generated on 07/28/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[64007-1100](#)